


SpeedyTie®

Features and Benefits


The SpeedyTie® can be used many times because of its removable, patented trigger. Also this is a heavy duty releasable tie that can bear loads of up to 888N (200lbs). With a length of 750mm it suits a wide variety of applications and is easy to handle even when wearing work gloves. Any excess tail can be easily 'tucked away' in a second slot on the head. These ties are available in 'high visibility' yellow and in weatherproof black.

Application

The versatility of the SpeedyTie® means that it is suitable for a multitude of applications. Originally developed for the 'offshore' industries, other uses include: construction, electrical installations, scaffolding sheet installations, exhibitions, trade fairs, and many more.



Patented quick release mechanism for quick and easy application.




SpeedyTie®



SpeedyTie® - Quick and easy.



Excess Tails can be neatly tucked away.



SpeedyTie® is particularly suited for temporary but safe bundling or fixing.

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Colour	Material	Pack Cont.
115-00000	RTT750HR	750	13	210	888	Yellow (YE), Red (RD)*	PA66	25
115-00001	RTT750HR	750	13	210	888	Yellow (YE), Red (RD)*	PA66	5
115-00030	RTT750HR	750	13	210	888	Black (BK), Black (BK)*	PA66HIR(S)	5

All Dimensions in mm. Subject to technical changes.

* Fastener

Material Data	
RoHS	Material
Operating Temperature	Polyamide 6.6 (PA66) -40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2

HF
(halogenfree)

Material Data	
RoHS	Material
	Polyamide 6.6 High Impact Modified scan black (PA66HIR(S))
Colour	Black (BK), Black (BK)
Operating Temperature	-40 °C to +80 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 HB