




M-2299

5



Ø.156±.010
[4.0]
MOUNTING HOLES



NOTES:

1. WIRE CAPACITY #18-#14 AWG, SOLID OR STRANDED COPPER WIRE ONLY.
2. ALL DIMENSIONS IN INCHES.
[mm]

CODE 74545

TITLE

15A 125/250V 3 WIRE
MIDGET TWIST-LOCK
FLANGED RECEPTACLE
NEMA ML-3R

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BODY	PHENOLIC	BLACK
CONTACT SPR. BIND. PL.	031 BRONZE	
CENTER CONTACT	BRASS	
BINDING SCREWS	BRASS	
INSULATING BARRIER	NYLON	BLACK
CUPPED WASHER	BRASS	
INSULATOR	NYLON	NATURAL
CASING	STAIN. STEEL	
NEUTRAL BIND. SCREW	BRASS	NICKEL PL.
BASE	NYLON	

5	REDRAWN ON NEW FORMAT, WAS "A" SIZE; CASING: STAIN. STEEL WAS BRASS; CONVERTED DIMS FROM FRACTION TO DECIMAL; ADDED NOTES 1 & 2 PER DCN 16134 RCM	DJP	11/19/09
---	---	-----	----------

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

SUPERSEDES DWG DATED 8/20/43

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS ± 1/64
DECIMALS ± .005
ANGLES ± 2°

HARVEY HUBBELL, INC.
BRIDGEPORT, CONN.

DR. BY A.J.Z. APP. BY
TR. BY RCM SCALE FULL
CHK'D. BY DATE 11/19/09

DIMENSION SHEET FOR CAT. NO.
HBL7489

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-2299

5