


# Machine Tube Luminaire




**RL70CE- 136 H**

|                         |  |
|-------------------------|--|
| connected load          | 110-230V; 50/60Hz  |
| fitted with             | 1 x compact fluorescent lamp TC-L 36 W<br>neutral white 4000 K |
| work equipment          | electronic ballast   |
| mains lead              | direct supply  |
| luminaire body material | borosilicate glass   |
| luminaire base form     | I  |
| weight (net)            | approx. 2 kg   |
| fastening               | lamp bracket (accessory)                                       |
| technology              | switchable   |
| usage                   | without switch   |
| light distribution      | direct   |
| system of protection    | IP 67  |
| class of protection     | I  |
| total length            | 584  |
| light output            | 395mm  |
| outside diameter        | 70 mm  |
| article no.             | C with screwed cable gland<br>619063001                        |



E<sub>min</sub>: 192 lx  
E<sub>m</sub>: 280 lx  
E<sub>max</sub>: 354 lx



measuring conditions: d=100cm

