



## Test Report

No. 2022757/EC

Date : Jun 30 2005

Page 1 of 2

MULTICOMP PRODUCTS MANUFACTURED BY  
CONTINENTAL DEVICE INDIA LIMITED  
C-120 NARAINA INDUSTRIAL AREA,  
NEW DELHI - 110 028 INDIA

Report on the submitted sample said to be GENERAL PURPOSE RECTIFIERS

SGS Job No. : 1763552  
Part Description : 1N4000 SERIES (DO-41P AXIAL LEADED PLASTIC PACKAGE)  
Buyer : PREMIER FARNELL ASIA PTE LTD  
Supplier : CONTINENTAL DEVICE INDIA LIMITED  
Sample Receiving Date : MAY 12 2005  
Testing Period : MAY 13 - 24 2005

Test Requested : With reference to RoHS Directive 2002/95/EEC  
1) To determine the Cadmium Content in the submitted sample.  
2) To determine the Lead Content on the submitted sample.  
3) To determine the Mercury Content on the submitted sample.  
4) To determine the Hexavalent Chromium Content on the submitted sample.  
5) To determine the Cadmium, Lead and Mercury content in the submitted metal sample.  
6) Determination of PBBs (Polybrominated biphenyls), PBDEs (Polybrominated diphenylethers) of the submitted sample.

Test Method : 1) As specified in BS EN 1122:2001, Method B, analysis was performed by Inductively Coupled Argon Plasma – Atomic Emission Spectrometry (ICP-AES).  
2) As specified in EPA Method 3050B. Analysis was performed by Inductively Coupled Argon Plasma – Atomic Emission Spectrometry (ICP-AES).  
3) As specified in EPA Method 3052. Analysis was performed by Inductively Coupled Argon Plasma – Atomic Emission Spectrometry (ICP-AES).  
4) As specified in EPA Method 3060A & 7196A. The sample was alkaline digested by using EPA Method 3060A, and then analyzed by using Colorimetric method 7196A.  
5) In house method. The sample was digested by acid. Analysis was performed by Atomic Absorption or Inductively Coupled Argon Plasma – Atomic Emission Spectrometry (ICP-AES).  
6) With reference to SGS in-house method. Analysis was performed by GC/MS.

Test Results : 1-6) Please refer to next page.

Conclusion : 1-6) When tested as specified, the submitted samples comply with the requirements of RoHS Directive Consultation document on 2002/95/EC.

Signed for and on behalf of  
SGS Hong Kong Ltd

Ho Ka Ting, Family  
Laboratory Executive



## Test Report

No. 2022757/EC

Date : Jun 30 2005

Page 2 of 2

### Test Results :

1-5)

Element	1	2	Limit of RoHS Consultant Document
Cadmium (Cd)	< 2 ppm	< 2 ppm	100 ppm
Lead (Pb)	4 ppm	9 ppm	1000 ppm
Mercury (Hg)	< 2 ppm	< 2 ppm	1000 ppm
Hexavalent Chromium (Cr <sup>6+</sup> )	< 2 ppm	< 2 ppm	1000 ppm

(Results shown are of the total weight of samples)

Note: < = Less than  
ppm = mg/kg  
0.01% = 100 ppm

6)

Flame Retardants	1	2	Detection Limit	Limit of RoHS Consultant Document
<b>Polybrominated Biphenyls (PBBs)</b>	---	---	---	1000 ppm
Monobromobiphenyl	ND	ND	5 ppm	--
Dibromobiphenyl	ND	ND	5 ppm	--
Tribromobiphenyl	ND	ND	5 ppm	--
Tetrabromobiphenyl	ND	ND	5 ppm	--
Pentabromobiphenyl	ND	ND	5 ppm	--
Hexabromobiphenyl	ND	ND	5 ppm	--
Heptabromobiphenyl	ND	ND	5 ppm	--
Octabromobiphenyl	ND	ND	5 ppm	--
Nonabromobiphenyl	ND	ND	5 ppm	--
Decabromobiphenyl	ND	ND	5 ppm	--
<b>Polybrominated Diphenylethers (PBDEs)</b>	---	---	---	1000 ppm
Monobromodiphenyl ether	ND	ND	5 ppm	--
Dibromodiphenyl ether	ND	ND	5 ppm	--
Tribromodiphenyl ether	ND	ND	5 ppm	--
Tetrabromodiphenyl ether	ND	ND	5 ppm	--
Pentabromodiphenyl ether	ND	ND	5 ppm	--
Hexabromodiphenyl ether	ND	ND	5 ppm	--
Heptabromodiphenyl ether	ND	ND	5 ppm	--
Octabromodiphenyl ether	ND	ND	5 ppm	--
Nonabromodiphenyl ether	ND	ND	5 ppm	--
Decabromodiphenyl ether	ND	ND	5 ppm	--

Note: ND = Not Detected

Non-detected is lower than detection limit value.

### Sample Description:

1. Black Plastic w/ Silvery Printing (Body)
2. Silvery Metal w/ Bronze Metal (Pin)

Remark : Photo appendix is included

\*\*\* End of Report \*\*\*

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.


H11991866



Test Report No. : 2022757/EC


Sample Receiving Date : MAY 12 2005

### PHOTO APPENDIX



SGS authenticate the photo on original report only

Page 1 of 1

  
Authorized Signature  
Ho Ka Ting, Family  
Laboratory Executive

This test document cannot be reproduced in any way, except in full context, without prior approval in writing from SGS.