

N-Channel JFETs

PRODUCT SUMMARY				
Part Number	$V_{GS(off)}$ (V)	$V_{(BR)GSS}$ Min (V)	g_{fs} Min (mS)	I_{DSS} Min (mA)
J304	-2 to -6	-30	4.5	5
J305	-0.5 to -3	-30	3	1

FEATURES

- Excellent High Frequency Gain: J304, Gps 11 dB (typ) @ 400 MHz
- Very Low Noise: 3.8 dB (typ) @ 400 MHz
- Very Low Distortion
- High ac/dc Switch Off-Isolation
- High Gain: $A_V = 60$ @ 100 μ A

BENEFITS

- Wideband High Gain
- Very High System Sensitivity
- High Quality of Amplification
- High-Speed Switching Capability
- High Low-Level Signal Amplification

APPLICATIONS


- High-Frequency Amplifier/Mixer
- Oscillator
- Sample-and-Hold
- Very Low Capacitance Switches

DESCRIPTION

The J304/305 n-channel JFETs provide high-performance amplification, especially at high-frequency. These products are available in tape and reel for automated assembly (see Package Information).

For similar products in TO-236 (SOT-23) packages, see the 2N/SST5484 series data sheet, or in TO-206AF (TO-72) packages, see the 2N/SST4416 series data sheet.

**TO-226AA
(TO-92)**



Top View

ABSOLUTE MAXIMUM RATINGS

Gate-Source/Gate-Drain Voltage	-30 V
Forward Gate Current	10 mA
Storage Temperature	-55 to 150°C
Operating Junction Temperature	-55 to 150°C

Lead Temperature ($1/16$ " from case for 10 sec.)	300°C
Power Dissipation ^a	350 mW

Notes

- a. Derate 2.8 mW/°C above 25°C

SPECIFICATIONS (T _A = 25 °C UNLESS OTHERWISE NOTED)								
Parameter	Symbol	Test Conditions	Typ ^a	Limits				Unit
				J304		J305		
				Min	Max	Min	Max	
Static								
Gate-Source Breakdown Voltage	V _{(BR)GSS}	I _G = -1 μA, V _{DS} = 0 V	-35	-30		-30		V
Gate-Source Cutoff Voltage	V _{GS(off)}	V _{DS} = 15 V, I _D = 1 nA		-2	-6	-0.5	-3	V
Saturation Drain Current ^b	I _{DSS}	V _{DS} = 15 V, V _{GS} = 0 V		5	15	1	8	mA
Gate Reverse Current	I _{GSS}	V _{GS} = -20 V, V _{DS} = 0 V			-100		-100	pA
			T _A = 100 °C	-0.2				nA
Gate Operating Current ^b	I _G	V _{DG} = 10 V, I _D = 1 mA	-20					pA
Drain Cutoff Current	I _{D(off)}	V _{DS} = 10 V, V _{GS} = -6 V	2					
Drain-Source On-Resistance	r _{DS(on)}	V _{GS} = 0 V, I _D = 300 μA	200					Ω
Gate-Source Forward Voltage	V _{GS(F)}	I _G = 1 mA, V _{DS} = 0 V	0.7					V
Dynamic								
Common-Source Forward Transconductance	g _{fs}	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 kHz		4.5	7.5	3		mS
Common-Source Output Conductance	g _{os}				50		50	μS
Common-Source Input Capacitance	C _{iss}	V _{DS} = 15 V, V _{GS} = 0 V f = 1 MHz	2.2					pF
Common-Source Reverse Transfer Capacitance	C _{rss}		0.7					
Common-Source Output Capacitance	C _{oss}		1					
Equivalent Input Noise Voltage	\bar{e}_n	V _{DS} = 10 V, V _{GS} = 0 V f = 100 Hz	10					nV/ √Hz







TYPICAL HIGH-FREQUENCY SPECIFICATIONS (T _A = 25 °C UNLESS OTHERWISE NOTED)								
Parameter	Symbol	Test Conditions	Limits (Typ)				Unit	
			J304		J305			
			100 MHz	400 MHz	100 MHz	400 MHz		
High-Frequency								
Common-Source Input Conductance	g _{iss}	V _{DS} = 15 V, V _{GS} = 0 V	80	800	80			μS
Common-Source Input Susceptance	b _{iss}	V _{DS} = 15 V, V _{GS} = 0 V	2	7.5	2			mS
Common-Source Output Conductance	g _{oss}		60	80	60			μS
Common-Source Output Susceptance	b _{oss}		0.8	3.6	0.8			mS
Common-Source Forward Transconductance	g _{fs}		4.4	4.2	3			
Common-Source Power Gain	G _{ps}	V _{DS} = 15 V, I _D = 5 mA	20	11				dB
Noise Figure	NF	R _G = 1 kΩ	1.7	3.8				

Notes

- a. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- b. Pulse test: PW ≤ 300 μs, duty cycle ≤ 2%.







NH

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)
Drain Current and Transconductance vs. Gate-Source Cutoff Voltage

On-Resistance and Output Conductance vs. Gate-Source Cutoff Voltage

Gate Leakage Current

Common-Source Forward Transconductance vs. Drain Current

Output Characteristics

Output Characteristics





TYPICAL CHARACTERISTICS (T_A = 25°C UNLESS OTHERWISE NOTED)






TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)


Common-Source Input Capacitance vs. Gate-Source Voltage




Common-Source Reverse Feedback Capacitance vs. Gate-Source Voltage




Input Admittance




Forward Admittance



Reverse Admittance





Output Admittance





TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)



Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?70236>.



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.