


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/22/03	B.MAZEJKA
B	ECN#2456: ADDED GAP BETWEEN CAP AND CHAIN RETAINING SCREW	06/27/06	D.PARHAM
C	ECN 4303: REVISED PACKAGING NOTE FOR PS-0031.	10/2/09	D.FRISIELLO
D	ECN 8732:CHNAGE CAP MATERIAL ,UPD L-COM LOGO, DWG FORM&ROHS	04/20/17	D.CUI



NOTES:

MATERIAL :
 CAP: PC+ABS, BLACK
 GASKET: EPDM, BLACK
 CHAIN: BRASS
 SCREW: STAINLESS STEEL
 HARDWARE: STAINLESS STEEL

FINISH:
 CHAIN: NICKEL PLATED, 40μ INCHES

MISCELLANEOUS:
 INGRESS RATING: IP67(MATED)
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY B.MAZEJKA	12/09/2003		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.3]	CHECKED BY D.PARHAM	12/09/2003	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY McCORMICK	12/09/2003	WATERPROOF CAP, USB	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	SCALE: NONE	CAD FILE: WPUSB-CVR.SLDDRW	DWG. NO. WPUSB-CVR	REV. D
			SHEET 1 OF 1	