NOTES:

I. MATERIALS AND FINISHES:

BODY - BERYLLIUM COPPER, ALBALOY PLATING
CONTACT PIN - BERYLLIUM COPPER, GOLD PLATING INSULATORS - PTFE, NATRUAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC - 6 GHz
C. VSWR: I.15 @ DC - 3 GHz
I.20 @ 3 - 6 Ghz

3. MECHANICAL:


A. TEMPERATURE RANGE: -55° C TO 125° C

4. PACKAGING:


A. QUANTITY: SINGLE PACK
B. MARKING: "AMPHENOL RF, AD-SMAJHDEFIP-I, DATE CODE"

THIRD ANGLE PROJ. 🕀 🖯

REVISIONS DESCRIPTION DATE ECN APPR REV Α RELEASE TO MFG. 06-Aug-18 8787 BMG



SCALE 5.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:	MATERIAL	DRAWN	DATE	TITLE	
<pre> <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°</pre>	CEE MOTEC	B. GREENBAUM	11-Jun-18	L SMA JACK TO	Amphenol Rh
NOTICE - These drawings, specifications, or other data (I) are, and remain the	SEE NOTES	ENGINEER	DATE	HD-EFI PLUG	
property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they	REFERENCE	B. GREENBAUM	11-Jun-18		www.amphenolrf.com
are given by Amphenol Corp. the furnishing of these drawings, specifications, of	EAR# 8375	APPROVED	DATE	ADAPTER	DRAWING NO. AD-SMAJHDEFIP-I
other data by Amphenol Corp., or to any other person to anyone for any purpose in not to be regarded by implication or otherwise in any manner licensing, granting	REF: SMAF-DFIFI-AT5GP-50	K. CAPOZZI	06 - Aug - 18	SCALE: 10.0:1.0 SHEET 2 OF 2	
rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be	CONFIGURATION LEVEL: In Work	CAD FILE		DWG SIZE REV	
related to or disclosed by said drawings, specifications, or other data.	FINISH			В А	PART NO. AD-SMAJHDEFIP-I