

Where to buy ?

Interactive
Catalog HomeProduct Family
InformationSpecification
SearchSearch
Help**Lever NOT Included**

Representative photograph, actual product appearance may vary.

- [Installation Instructions](#)
- [Lever - Required Accessory](#)
- [Specifications](#)

Click here for a print friendly version of this datasheet.

EX-AR20

Explosion-Proof Limit Switches Series EX: Side Rotary; 1NC 1NO SPDT Snap Action; 0.5 in - 14NPT conduit

Features

- NEMA 1, 7, and 9
- Compact, rugged housing
- Up to 20 amp capacity
- Ample wiring space
- Mounts from four sides
- Roller arms adjustable through 360 degrees
- Non-sparking actuators
- Captive cover screws
- UL listed, file #E14274
- CSA certified, file #LR57324
- ATEX approved, file #KEMA 04ATEX2312 X
- Grounding screw

Typical Applications

- Control valves and actuators
- Petro-chemical plants
- Conveyors
- Material handling

Description

EX switches feature the smallest UL-listed housings available for use in hazardous locations. Flame paths within the housing cool exploding gases below the kindling temperature before they reach the explosive gases surrounding the housing.

Product Specifications

| Product Specifications | |
|----------------------------|---|
| Availability | Global |
| Operating Force (O.F.) | 0,22 Nm [31.25 in/oz] |
| Pretravel (P.T.) | 5,56 mm [0.219 in] (8°) max. |
| Overtravel (O.T.) | 90° max. |
| Differential Travel (D.T.) | 0,18 mm [0.007 in] (0.25°) max. |
| Product Type | Explosion-Proof Limit Switches |
| Actuator | Side Rotary |
| Lever Style | Lever Not Included - Reference Lever Required Accessory |
| Circuitry | 1NC 1NO SPDT Snap Action |
| Ampere Rating | 15 A Ind./ 0.5 A Res./0.25 A Res. |
| Supply Voltage | 125 Vac, 250 Vac, 480 Vac/125 Vdc/250 Vdc |

| | |
|------------------------------------|--|
| Housing Material | Aluminum |
| Termination Type | 0.5 in - 14NPT conduit |
| Housing Type | EX |
| Series Name | EX Series |
| Sealing | NEMA 1, 7 (Class I, Division 1, Groups C, D), 9 (Class II, Division 1, Groups E, F, G) |
| Approvals | UL listed, CSA Certified, ATEX approved |
| CSA File # | LR57324 |
| UL File # | E14274 |
| ATEX File # | KEMA 04ATEX2312 X |
| Operating Temperature Range | -40 °C to 71 °C [-40 °F to 160 °F] |
| Comment | CW Actuation; No Lever furnished with switch |
| Sealed | Explosion-proof |

Due to regional agency approval requirements, some products may not be available in your area. Please contact your regional Honeywell office regarding your product of choice.