


Sep.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

1		2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
△					△					



NOTES 1 APPLICABLE CRIMP CONTACT:
 HR12-SC-212(CL112-0408-9)
 APPLICABLE WIRE:AWG#26 TO #30
 (COVERED WIRE MAX,OUTSIDE DIA.φ 1)
 APPLICABLE CONTACT REMOVAL TOOL
 (EXTRACTION TOOL):HR12-SC-TP(CL150-0050-3)
 ② APPLICABLE CRIMPING TOOL OF REF.NO.⑦:
 HR10A-TC-02(CL150-0041-2)
 THE HOLE DIAMETER FOR CRIMPING:φ 5.3
 ③ THE RECOMMENDED CLAMP TORQUE, REF.NO.⑤
 : 1.5 TO 2 N·m.
 ④ ACROSS FLATS HEXAGON HEAD OF REF.NO.⑥: 1.27
 THE RECOMMENDED CLAMP TORQUE,
 REF.NO.⑥: 0.3 TO 0.4N·m.
 THE TIP OF REF.NO.⑥ SHALL BE FIXED TO
 THE CONCAVE PORTION WITH REF.NO.⑦ CLAMPED
 TO THE CABLE.
 ⑤ LOCTITE 242,HENKEL JAPAN OR EQUIVALENT IS
 RECOMMENDED TO PREVENT REF.NO.① AND ⑥
 FOR LOOSENING.
 6 ONE EXAMPLE OF THE ROTATION OF REF.NO.⑤ TO
 REF.NO.① IS SHOWN.
 7 THE CABLE PULL AND TWISTING STRENGTH AND
 OTHER CHARACTERISTICS MAY DIFFER,
 DEPENDING ON THE CABLE STRUCTURE.
 PLEASE CONFIRM BEFORE THE USE.

4	STEEL	NICKEL PLATING	8	CHLOROPRENE RUBBER	(BLACK)
3	BRASS	MATTE FINISH NICKEL PLATED	7	BRASS	
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	6	STEEL	NICKEL PLATING M2.6×0.45×2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWN <i>M. Sato</i> 07.03.07	DESIGNED <i>T. Horii</i> 07.03.07	CHECKED <i>E. Humei</i> 07.03.08	APPROVED <i>M. Sato</i> 07.03.08	RELEASED
DRAWING NO. EDC4-025174-73		PART NO. HR10A-7P-4SC(73)				
SCALE 2 : 1		CODE NO. CL110-0502-4-73				1/1
UNITS mm		HRS HIROSE ELECTRIC CO.,LTD.				

TO
R