





Sep.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.



- NOTES 1 THIS PRODUCT IS APPLY TO THE WIRE AWG#30(WIRE JACKET DIAMETER ϕ 0.71 MAX).
- 2 PER PACK : 100 CONTACTS.
- 3 RECOMMEND CABLE PREPARATION DIMENTION ARE SHOWN IN FIG.1.
- 4 APPLICABLE OPERATION CRIMP TOOL:HR25-TA3032HC

				1	PHOSPHER BRONZE		CONTACT AREA: GOLD 0.2μm min. TERMINAI AREA:NICKEL PLATING 1μm min. UNDER PLATING: NICKEL PLATING 1μm min.					
NO.	MATERIAL		FINISH . REMARKS			NO.	MATERIAL		FINISH . REMARKS			
UNITS mm		SCALE 10 : 1		COUNT		DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
 HIROSE ELECTRIC CO., LTD.			APPROVED :EJ. KUNII			15.10.05	DRAWING NO.		EDC-110401-00-00			
			CHECKED :EJ. KUNII			15.10.05	PART NO.		HR25-SC-111			
			DESIGNED :WR. AJIRO			15.10.05	CODE NO.		CL125-0421-3-00			
			DRAWN :WR. AJIRO			15.10.05						
											1/1	