



In case that the application demands a high level of reliability, such as automotive, please contact a company representative for further information of relevant legislation.

REVISIONS				DATE				
	DESCRIPTION OF REVISIONS	B Y	CHKD	COUNT	DESCRIPTION OF REVISIONS	B Y	CHKD	DATE
<				<				.
<				<				.
<				<				.



B DETAIL OF MOUNTING GUIDE

NOTE 1 $\triangleright$ RECOMMENDED CLAMP TORQUE OF REF NO. ⑥ : 2-2.5 N · m.
LOCTITE 242, HEIKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF.NO. ⑥ FROM LOOSENING.



PANEL CUTOUT
 $t = 0.8 \sim 1.5$

4	POLYAMIDE	(BLACK) UL94V-0			
3	BERYLLIUM COPPER	SILVER PLATING 2 μ m min.	7	PHOSPHOR BRONZE	NICKEL PLATING
2	BERYLLIUM COPPER		6	BRASS	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING	5	STAINLESS STEEL	
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	D. Mathame '05-10-01	D. Mathame '05-10-01	E. Kurui 105-10-03	M. Sato 05-10-14	

	DRAWING NO. EDC3-045401-73	PART NO. HR10A-13R-20S(73)
SCALE 2 : 1	 HIROSE ELECTRIC CO.,LTD.	CODE NO. CL110-0714-2-73
UNITS mm		1/1

TO	R			
----	---	--	--	--