

## Polyurethane Tubing Series TU

- Flexible tubing
- For general industrial air and water applications
- ✓ 20m and 100m coils
- 8 colour option
- Available in metric size (TU) and inch size (TIUB) CONTACT SMC FOR DETAILS OF LARGER LENGTH AND INCH SIZES (SERIES TIUB).




#### TECHNICAL SPECIFICATIONS

Note 1) The value for bending at a temperature of 20°C Note 2) Safety allowance see burst pressure chart
Note 3) To calculate flow factor for longer lengths of tube
divide factor for 1 metre by √actual length in metres.

Model	TU0425-20	TU0604-20	TU0805-20	TU1065-20	TU1208-20		
Tube OD (mm)	4	6	8	10	12		
Tube ID (mm)	2.5	4	5	6.5	8		
Max operating pressure	8 Bar <sup>Note 2)</sup> (0.8MPa)						
Coil length	20m						
Note 1) Min bending radius (mm)	10	15	20	27	35		
Flow factor Cv/metre	0.11	0.39	0.70	1.41	2.45		
Operating temperature	-20~+60°C						
Material		Polyurethane					

#### How To ORDER POLYURETHANE TUBING SERIES TU




1065......10mm O.D. 6.5mm I.D. 1208.....12mm O.D. 8mm I.D.

### STOCKED PRODUCTS FOR A LIST OF STOCKED PRODUCTS,

LEASE SEE THE CURRENT SMC PRICE LIST

#### BURST PRESSURE CHARACTERISTICS CURVE





- 1) Applicable for general industry water. Consult SMC if using for other kind of fluid. Surge pressure must be under the max. operating pressure. If exceeding that value, fitting may be damaged and tubing may burst.
- 2) The values of the max. operating pressure are at a temperature of 20°C. Refer to the Burst Pressure Characteristics Curve for other temperatures. Avoid abnormal temperature rise which may burst the tubing.
- 3) The values of the min. bending radius are at a temperature of 20°C. Higher temperature allows the tubing to be bent more.





## SOFT POLYURETHANE TUBING SERIES TUS

✓ Suitable for piping in confined space

✓ 20m and 100m coils

✓ 8 colour option



#### SERIES TABLE

Model	TUS0425	TUS0604	TUS0805	TUS1065	TUS1208
Tube O.D. (mm)	4	6	8	10	12
Tube I.D. (mm)	2.5	4	5	6.5	8
Black (B)					
White (W)					
Red (R)					
Blue (BU)					
Yellow (Y)					
Green (G)					
Translucent (N)					
Yellow Brown (YB)					

■ 20m roll

■ 20m & 100m roll




Model		TUS0425	TUS0604	TUS0805	TUS1065	TUS1208		
Operating Fluid				Air				
Max Operating Pres	sure		0.6MI	a {6.1kgf/cm²} at 2	20°C			
Burst Pressure		F	efer to burst p	ressure chara	cteristics curve			
Applicable tube fitti	ng	One to	One touch fitting, insert tube fitting, hose nipple (Note 2)					
Min. Bending radius	(mm) (Note 1)	8	15	15	22	29		
Operating temperat	ure	-20 to +60°C						
Material				Polyurethane				
Tube drawing	Without inner sleeve	15	60	60	85	110		
strength N								
(Using One touch fitting)	With inner sleeve	80	230	250	300	480		

Note 1) Min. bending radius is measured as shown in figure below Note 2) Always use inner sleeve (series TJ) in safety circuit or critical area

end Fixed

Bend the tube into U-form at a temperature of 20°C. Fix one end and close loop gradually Measure 2R when the tube breaks or is crushed.

How To ORDER POLYURETHANE TUBING SERIES TUS



. Yellow .....Green .Translucent YB ... YellowBrown






#### TUS RELATED ACCESSORIES INNER SLEEVE


#### SERIES TJ

Reinforces soft polyurethane tubing. Insert an inner sleeve into soft polyurethane tubing when used with one touch fitting.



Part No.	Applicable Tube Model	Length (mm)
TJ-0425	TUS0425	18
TJ-0604	TUS0604	19
TJ-0805	TUS0805	20.5
TJ-1065	TUS1065	23
TJ-1208	TUS1208	24

#### BURST PRESSURE CHARACTERISTICS CURVE





## Anti-static Polyurethane Tubing Series TAU

For further information see anti-static one touch fittings Series KA



# FLAME RESISTANT NYLON TUBING SERIES TRS SINGLE LAYER TUBING SERIES TRB DOUBLE LAYER TUBING

See flame resistant one touch fittings series KR/KRM page 4-75 for more information.



## General Purpose Nylon Tubing Series SMC and TS

See Section 10 for more information



# HOW TO ORDER POLYURETHANE FLAT TUBING SERIES TFU


TFU  $\bigcirc$  B  $-\bigcirc$ 

Number of Tubes -

2 ......2 3



#### Burst Pressure Characteristics Curve



## POLYURETHANE FLAT TUBING SERIES TFU

2 or 3 core flat tubing for neat presentation

### Technical Specifications

Model	TFU 0425B-2	TFU 0425B-3	TFU 0604B-2	TFU 0604B-3	TFU 0805B-2	TFU 0805B-3	
Number of tubes	2	3	2	3	2	3	
Tube OD (mm)	4	1	(	5	8		
Tube ID (mm)	2.	.5	4		5		
Flow factor Cv/metres <sup>ote 3)</sup>	0.	11	0.39		0.70		
Max operating pressure			8 Bara	t 20°C			
Operating temperature			-20to	+60°C			
Material		Polyurethane					
Colour	Black						
Note 1) Min bending radius (mm)	1	0	1	5	2	0	
Tube length per roll (m)	10						

Note 1) The value for bending at a temperature of 20  $^{\circ}\text{C}$ 

#### STOCKED PRODUCTS FOR A LIST OF STOCKED PRODUCTS, PLEASE SEE THE CURRENT SMC PRICE LIST

Contact SMC for colour options, larger lengths, number of tubes option





## **SMC**

## POLYURETHANE COIL TUBING SERIES TCU

✓ Single or multi-core option

✓ For flexible piping applications



#### TECHNICAL SPECIFICATIONS

Fittings & Tubing

OI LOII 107 (1110140								
Model	TCU 0425B-1	TCU 0425B-2	TCU 0425B-3	TCU 0604B-1	TCU 0604B-2	TCU 0604B-3	TCU 0805B-1	
Number of tubes core	1 2		3	1	2	3	1	
Tube OD (mm)		4			6		8	
Tube ID (mm)	2.5			4			5	
Max operating pressure		See burst pressure chart						
Operating temperature		-20~+60°C						
Material		Polyurethane						
Colour		Black						
Operating Fluid		Air Note 2						

Note 1) The value for bending at a temperature of 20°C Note 2) Consult SMC if using other than air

How To Order Polyurethane Coil Tubing Series TCU

TCU B —

0425 . . 4mm O.D. 2.5mm I.D. 0604 . . 6mm O.D. 4mm I.D. 0805 . . 8mm O.D. 5mm I.D.


No. of Tubes -

2 .....2

STOCKED PRODUCTS
FOR A LIST OF STOCKED PRODUCTS,
PLEASE SEE THE CURRENT SMC PRICE LIST


Consult SMC for change of coil turns or colour change

#### Burst Pressure Characteristics Curve



### DIMENSIONS

POLYURETHANE COIL TUBING



Specifications	Tube siz	ze (mm) Dimension		of coil (mm)	Number of tube	Number of coil winding per	Max operating	
Model	OD	ID	L	D	core	tube length	length (m)	
TCU0425B-1			210	18	1	52	1.5	
TCU0425B-2	4	2.5	280	28	2	35	1.5	
TCU0425B-3			265		3	22	1	
TCU0604B-1			325	24	1	54	2	
TCU0604B-2	6	4	323	37	2	27	1.5	
TCU0604B-3			305	305	37	3	17	1



### MULTITUBE HOLDER SERIES TM

Arranges tubes neatly

Accepts Ø4mm~12mm

✓ 6-12 tube design

✓ Uses flame resistant resin (V-0)



Tube material	Nylon, Soft nylon, Polyurethane
Tube O.D.	Ø4, Ø6,Ø8,Ø10, Ø12
Ambient (°C)	-20~60
Material	Flame resistance polypropylene (UL-94 standard V-0)
Colour	Black



How To ORDER TM MULTITUBE HOLDER



...4mm (12 connecting tubes) ...6mm (12 connecting tubes) ...8mm (8 connecting tubes) ...10mm (6 connecting tubes)

0.6 0.8


...12mm (6 connecting tubes)

Dimensions in mm

Dimensions in mm

Safety lock (loosened)

**DIMENSIONS** 



Applicable tube O.D.	Model	N (Number of	Р	L1	L2	W1	W2	W3	H1	H2	ØD	Mounting tapping screw size
(mm)		holding parts)										Nominal x Length
4	TM-04	12	6	3.25	72.5	4.5	8	17	5	7.5	2.2	M2x6
6	TM-06	12	7.5	4.5	91.5	5.5	10	21	6.5	10	2.8	M2.6x8
8	TM-08	8	9.5	5.5	77.5	6	11	23	7.5	12	2.8	M2.6x8
10	- TM-10	6	12.5	7.5	77.5	6.5	12	25	8.8	14.3	3.2	M3x8
12	TM-12	6	15	9	93	6.5	12	25	9.8	16.3	3.2	M3x8

DIMENSIONS TK1 TUBE CUTTER (TK2 TUBE CUTTER)

## Tube Cutter Series TK

✓ Perpendicular cutting Enclosure/safety lock contained



Model	TK-1	TK-2	TK-3				
Applicable tube material	Nylon, soft nylon, polyurethane, and other soft plastic tube						
Applicable tube O.D.	13mm or less	18mm or less	12mm or less				





SPECIFICATIONS							
Model	TK-1	TK-2	TK-3				
Applicable tube material	Nylon, soft nylon, polyurethane, and other soft plastic tube						
Applicable tube O.D.	13mm or less	18mm or less	12mm or less				



TK - 1


TK - 2

TK - 3






Never cut electric wire metals



155 (176)







## TUBING & ACCESSORIES



### TUBE STAND SERIES TB-1

- Used in conjunction with series TBR tube reels to provide practical storage and dispensing solutions
- Mounted on lockable castors
- ✓ Tube cutter tray
- ✓ Easy to load



### TUBE REEL SERIES TBR-1~4

- Specifically designed for installing 100m coils of tube in reel stand TB-1
- Easy loading of tube onto the reel
- Easy dispensing of tube









TBR-1	for Ø4mm, Ø6mm tube
TBR-2	for Ø8mm tube
TBR-3	for Ø10mm tube
TRR-4	for Ø12mm tube




Side Board	Grey	Polyurethane	
Side Board	Transparent	Polyurethane	
Core	-	PVC	
2 x hex bolt & wingnut	steel	M6(JIS std)	









	ØD	Ød	t	Н	W
TBR-1	Ø480	Ø230	-	84	50
TBR-2	Ø480	Ø230	1	134	100
TBR-3	Ø480	Ø230	1	184	150
TBR-4	Ø480	Ø230	1	234	200