


DO NOT SCALE DRAWING

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	22-10-2018	



Part No.	G	SW	ØD	H	A
TRKNF-30	M3	6.9	8.1	4.2	1.9
TRKNF-40	M4	7.9	9.7	4.8	2.0
TRKNF-50	M5	9.9	12.1	5.8	2.1
TRKNF-60	M6	12.7	15.0	6.9	2.6

NOTES :

Also available in flame retardant nylon(PA66 UL94V-0).

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS.
SURFACE FINISH:
TOLERANCES:
L≤4 = ±0.1 4<L≤15 = ±0.2
15<L≤50 = ±0.3 50<L≤100 = ±0.4

MATERIAL
PA66 UL94V-2
ROHS COMPLIANT

TITLE

KWIK NUT

NAME	DATE
DRAWN MARTIN ELLIOTT	22/10/2018
CHK'D	
APP'D	

HEAT TREATMENT

N/A

DESIGN RIGHT. TR FASTENINGS LTD. 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED.
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

CUSTOMER PART NO.

FINISH

BLACK

DWG NO.

TRKNF-XX

A3