

6.06101.50 SBE 610

## 610 watt electronic hammer drill SBE 610

- Variospeed (V) electronics for infinitely variable speed change
- Thumbwheel for preselection of speed
- Compact, lightweight machine in pot design for permanent use
- Die cast aluminium gear housing for optimum heat dissipation and stability
- User-friendly guidance of machine exhaust in all working situations
- Clockwise and anticlockwise rotation
- Impact-proof Metabo quick-action keyless chuck Futuro Plus for quick tool change
- Spindle with hexagon recess for screwdriver bits
- Ergonomic housing design for ideal handling
- Side handle with drilling depth guide

### Comparative device characteristics

Torque	5 Nm
Drilling capacity in	
- Concrete	12 mm
- Steel	10 mm
- Softwood	20 mm
No load speed	0 - 3.100 /min
Rated input power	610 W
Output power	360 W
Rated load speed	1.900 /min
Maximum impact rate	62.000 /min
Collar diameter	43 mm
Drilling spindle thread	1/2" - 20 UNF
Chuck capacity	1,5 - 13 mm
Drilling spindle with hexagon recess	1/4" (6,35 mm)
Weight (without mains cable)	1,7 kg

### Scope of delivery

quick-action keyless chuck Futuro Plus, side handle, drilling depth guide, carry case