


M12, 90 BUSH, X8/8 H+S 84124806

2350797-X

GENERAL MARKET



SHOWN: FEMALE CONNECTOR WITH COVER

				tools			crimpin	g tools				
		A				*			Î			
	Conductor size	Conductor stripping	Jacket cutting	Hand tool	Contact positioner	Crimp Selection number*	Crimp tool	Crimp Die	Handle	Insert for handle	Connector assembly tool	

1-2823557-1

Recommended Contact crimping Recommended jacket

Cable preparation

734185-1

\*TOOL SETTING MUST BE VALIDATED ON CABLE USED

1-2823558-6

1-2823558-5

9	BAG 60	x100 mm	1	PC
8	воот	THERMO PLASTIC	1+1	PC
7	BACKNUT & CRIMP SLEEVE	BRASS, NICKEL PLATED	1	PC
6	CRIMP INSERT	BRASS, NICKEL PLATED	1	PC
5	90° KNEE	ZINC	1	PC
4	CRIMP CONTACT	BRASS, Au PLATED	8	PC
3	CONTACT HOLDER	THERMO PLASTIC	3+1	PC
2	CONTACT CARRIER	THERMO PLASTIC	1	PC
1	FRONT HOUSING	BRASS, NICKEL PLATED	1+1	PC
Pos.	DESCRIPTION	MATERIAL	QTY	UNIT

Crimp Flange insertion

1-2823560-1 1-2823561-1 1-2823564-1

Ø16.5				25.75
	_	43	Ø16.5	6.32

Coding

of

positions

Gender

Female

contacts

included

Connector

type

Right Angle Radox 8.2mm

Applicable on cable

Right Angle | TE Cat 7 cable TECC0011C7 | TE 2297799-1

Manufacturer PN

H&S 84124806

Category

Cat 7

Cat 7

Color

Blue

Black 8 x AWG24

8 x AWG24

M12 X-8 FEMALE CONNECTOR

ALL DIMENSIONS ARE FOR NOMINAL REFERENCE ONLY.

2350797-1 M12 X-F-8,90,CRIMP,CAT7,H&S 84124806

2350797-2 M12 X-F-8,90,CRIMP,CAT7,TE 2297799-1

- PACKAGING: 1 PIECE IN A BOX, CONTACTS INCLUDED.

PART NO

HV DESC

CUSTOMER

TE PN

В

D

- PACKAGING: 1 PIECE IN A BOX, CONTACTS INCLUDED.

  THE CONNECTOR IS AS PER IEC 61076-2-109.

  TEMPERATURE RANGE: WITH CABLE BOOT-40°C TO +70°C.

  WITHOUT CABLE BOOT -40°C TO +85°C.

  VIBRATION & SHOCK TEST CONDUCTED AS PER IEC 61373:61373 CAT 1 CLASS B & CAT 2.

  FIRE PERFORMANCE CONDUCTED AS PER EN45545-2 HL3 R22/R23, NFF16-101 AND NFF16-102.

  SPECIAL CRIMP FLANGE SYSTEM WITH CRIMP INSERT AND CRIMP SLEEVE SECURES THE EFFECTIVE OF THE PROPERTIES WITH CONDUCTIONS.
- SHIELDING OVER THE LIFETIME WITH EXTREMELY HARD CONDITIONS.

Description

- VIBRATION AND TORSION-PROOF CABLE STRAIN RELIEF FOR ROUGH ENVIRONMENT ACHIEVED BY HEXAGONAL CRIMP OF THE CRIMP SLEEVE OF THE CRIMP FLANGE SYSTEM.
- DEGREE OF PROTECTION: IP 67 (ONLY SCREW-LOCKED).

- DATA TRANSMISSION RATE: UP TO 10Gbit/SEC ACC. TO IEC 802.3an CATEGORY 6A. CURRENT RATING: 0.5A, NOMINAL VOLTAGE: 48V, CONTACT RESISTANCE:  $\leq$  5 m $\Omega$ , INSULATION RESISTANCE:  $\geq$  100 m $\Omega$ . DURABILITY:  $\geq$  250 MATING CYCLES

				1 03.		DESCRIPTION		WATERIAL		α	Oilii
THIS DRAWING IS A CO	ONTROLLED DOCUMENT.	DWN 16APR2019 GOPALAKRISHNA HV			_	TE	TE	Connoct	ivitv. L	- d	
		CHK 16APR2019 S EGBERT	TE Connectivity Ltd.								
DIMENSIONS:	TOLERANCES UNLESS	APVD 16APR2019	NAME								
OTHERWISE SPECIFIED:		S EGBERT		) X-	-COD	)FD RAII	FFMALF	FEMALE 8 CRIMP CON			ORS
	O PLC ± -	PRODUCT SPEC	'*' ' 2	-, ^	OOD	DED TO THE	1 = 1417 \===	0 011111		111201	0110
ф <sub>—</sub>	1 PLC ± – 2 PLC ± –	_					_				
		APPLICATION SPEC									
,	4 PLC ± – ANGLES ± –	_	SIZE	CAGE		DRAWING NO				RESTRI	CTED TO
MATERIAL	FINISH	WEIGHT	]A3	007	779	<b>C</b> -235	0797			-	_
	_	CUSTOMER DRAWING					SCALE —	SHEET	1 OF	1 RE	v A

2119000-1 | 601966-1 | 1-2823582-8 |

1470-19 (1/15)

NOTES:

В