

Type: **DILM150(RAC120)**

Article No.: **239587**


Sales text **Contactor,75kW/400V,AC operated**

Ordering information			
Connection technique			Screw terminals
Description			3 pole
Description			Springloaded terminals on the auxiliary and control circuit terminals
Rated operational current			
AC-3 380 V 400 V	I_e	A	150
Max. rating for three-phase motors, 50 – 60 Hz			
AC-3 220 V 230 V	P	kW	48
AC-3 380 V 400 V	P	kW	75
AC-3 660 V 690 V	P	kW	125
AC-4 220 V 230 V	P	kW	20
AC-4 380 V 400 V	P	kW	34
AC-4 660 V 690 V	P	kW	48
Conventional free air thermal current I_{th} = I_e AC-1 at 60 °C			
Open	$I_{th} = I_e$	A	190
Can be combined with auxiliary contact			DILM150-XHI(V).. DILM1000-XHI(V)..
Actuating voltage			RAC 120

Contact sequence



Notes concerning the product group



Accessories

- 1 Overload relay → [278442](#)
- 2 Suppressor → [281199](#)
- 3 Auxiliary contact module → [277376](#)
- Further actuating voltages → [277379](#)
- Accessories → [281227](#)

The DC operated contactors have integral suppressor circuits (DILM7 – DILM15: Varistor).

Contactors DILM115, DILM150 and DILM170 have a built-in suppressor circuit.

Mirror contact for DILM7–01 to DILM32–01

Contactor contact according to EN 50012

General			
Standards			IEC/EN 60947, VDE 0660, UL, CSA
Lifespan, mechanical			
AC operated	Operations	$\times 10^6$	10
DC operated	Operations	$\times 10^6$	10
Operating frequency, mechanical			
AC operated	Operations/h		3600
DC operated	Operations/h		3600
Climatic proofing			Damp heat, constant, to IEC 60068–2–78 Damp heat, cyclical, to IEC 60068–2–30

Ambient temperature			
Open		° C	–25...60
Enclosed		° C	–25...40
Storage		° C	... 40...+80
Mechanical shock resistance (IEC/EN 60068–2–27)			
Half-sinusoidal shock, 10 ms			
Main contacts			
N/O contact		g	10
Auxiliary contacts			
N/O contact		g	7
N/C contact		g	5
Mechanical shock resistance (IEC/EN 60068–2–27) when tabletop-mounted			
Half-sinusoidal shock, 10 ms			
Main contacts			
Thickness of material for busbar max.		g	10
Auxiliary contacts			
Min. rated current = rated uninterrupted current		g	7
N/C contact		g	5
Protection type			IP00
Protection against direct contact when actuated from front (IEC 536)			Finger- and back-of-hand proof
Weight			
AC operated		kg	2
DC operated		kg	2,1
Terminal capacity main cable			
Flexible with ferrule		mm ²	1 × (10 – 95) 2 × (10 – 70)
Stranded		mm ²	1 × (16 – 95) 2 × (16 – 70)
Solid or stranded		AWG	8...3/0
Flat conductor	Number of segments × width × thickness	mm	2 × (6 × 16 × 0.8)
Main cable connection screw/bolt			M10
Tightening torque		Nm	14

Terminal capacity control circuit cables			
Solid		mm ²	1 × (0.75 – 4) 2 × (0.75 – 4)
Flexible with ferrule		mm ²	1 × (0.75 – 2.5) 2 × (0.75 – 2.5)
Solid or stranded		AWG	18 – 14
Control circuit cable connection screw/bolt			M3.5
Tightening torque		Nm	1.2
Tool			
Main cable			
Hexagon socket-head spanner	SW	mm	5
Control circuit cables			
Pozidriv screwdriver		Size	2
Standard screwdriver		mm	0.8 × 5.5 1 × 6
Terminal capacity control circuit cables			
Solid		mm ²	1 × (0.75 – 2.5) 2 × (0.75 – 2.5)
Flexible		mm ²	1 × (0.75 – 2.5) 2 × (0.75 – 2.5)
Flexible with ferrule		mm ²	1 × (0.75 – 1.5) 2 × (0.75 – 1.5)
Solid or stranded		AWG	18 – 14
Tool			
Stripping length		mm	10
Screwdriver blade width		mm	3,5
Main conducting paths			
Rated impulse withstand voltage	U_{imp}	V AC	8000
Overvoltage category/pollution degree			III/3
Rated insulation voltage	U_i	V AC	1000
Rated operational voltage	U_e	V AC	1000
Safe isolation to VDE 0106 Part 101 and Part 101/A1			
between coil and contacts		V AC	690
between the contacts		V AC	690
Making capacity (p.f. to IEC/EN 60947)			
	Up to 690 V	A	2100

Breaking capacity			
220/230 V		A	1500
380/400 V		A	1500
500 V		A	1500
660/690 V		A	1200
Short-circuit rating			
Short-circuit protection maximum fuse			
Type "2" coordination			
400 V	gG/gL 500 V	A	250
690 V	gG/gL 690 V	A	250
Type "1" coordination			
400 V	gG/gL 500 V	A	250
690 V	gG/gL 690 V	A	250
AC			
AC-1 duty			
conv. therm. current 3 pole 50 – 60 Hz			
open			
at 40 ° C	I_{th}	A	190
at 50 ° C	I_{th}	A	180
at 55 ° C	I_{th}	A	170
at 60 ° C	I_{th}	A	160
enclosed	I_{th}	A	144
Conventional free air thermal current, 1 pole			
open	I_{th}	A	400
enclosed	I_{th}	A	360
AC-3 duty			
Rated operational current AC-3 open, 50 – 60 Hz, 3 pole			
220/230 V	I_e	A	150
240 V	I_e	A	150
380/400 V	I_e	A	150
415 V	I_e	A	150
440V	I_e	A	150
500 V	I_e	A	150
660/690 V	I_e	A	100
Motor rating			

220/230 V	P	kW	48
240V	P	kW	52
380/400 V	P	kW	75
415 V	P	kW	91
440 V	P	kW	95
500 V	P	kW	110
660/690 V	P	kW	125
AC-4 duty			
Rated operational current AC-4 open, 50 – 60 Hz, 3 pole			
220/230 V	I_e	A	65
240 V	I_e	A	65
380/400 V	I_e	A	65
415 V	I_e	A	65
440 V	I_e	A	65
500 V	I_e	A	65
660/690 V	I_e	A	50
Motor rating			
220/230 V	P	kW	20
240 V	P	kW	22
380/400 V	P	kW	34
415 V	P	kW	39
440 V	P	kW	41
500 V	P	kW	47
660/690 V	P	kW	48
DC			
of three-phase capacitors open			
DC-1 operation			
60 V	I_e	A	160
110 V	I_e	A	160
220 V	I_e	A	90
440 V	I_e	A	4,5
DC-3 operation			
60 V	I_e	A	160
110 V	I_e	A	160
220 V	I_e	A	40
440 V	I_e	A	1
DC-5 operation			
60 V	I_e	A	160

110 V	I_e	A	160
220 V	I_e	A	40
440 V	I_e	A	1
Current heat loss (3 pole)			
Current heat loss at I_{th}		W	30,7
Current heat loss at I_e to AC-3/400 V		W	27
Impedance per pole		m	0,4
Magnet systems			
Voltage tolerance			
AC operated	Pick-up	$\times U_c$	0,8...1,15
Drop-out voltage AC operated	Drop-out	$\times U_c$	0,25...0,6
DC operated	Pick-up	$\times U_c$	0,7...1,2
DC operated	Drop-out	$\times U_c$	0,15...0,6
Power consumption of the coil in a cold state and $1.0 \times U_c$			
50 Hz	Pick-up	VA	180
50 Hz	Sealing	VA	3,1
50 Hz	Sealing	W	2,1
60 Hz	Pick-up	VA	170
60 Hz	Sealing	VA	3,1
60 Hz	Sealing	W	2,1
50/60 Hz	Pick-up	VA	170 170
50/60 Hz	Sealing	VA	3,1 3,1
50/60 Hz	Sealing	W	2,1 2,1
DC operated	Pick-up	W	149
DC operated	Sealing	W	2.1
Duty factor		% DF	100
Switching times at 100 % U_c (approximate values)			
Main contacts			
AC operated			
Closing delay		ms	28...33
Opening delay		ms	35...41
DC operated			
Closing delay		ms	35
Opening delay		ms	30
Arcing time		ms	15

Permissible residual current with actuation of A1 – A2 by the electronics (with 0 signal).		mA	1
--	--	----	---


Electromagnetic compatibility (EMC)			
--	--	--	--

Emitted interference			to EN 60947–1
Interference immunity			to EN 60947–1


Notes			
--------------	--	--	--

Notes			The following applies to magnet systems, voltage tolerance, pickup voltage DC-operated DILM17 – DILM32: RDC 24 (Umin 24 V DC/Umax 27 V DC) RDC 60 (Umin 48 V DC/Umax 60 V DC) RDC 130 (Umin 110 V DC/Umax 130 V DC) RDC 240 (Umin 200 V DC/Umax 240 V DC) Example: $U_c = 0.7 \times U_{min} - 1.2 \times U_{max}$ $U_c = 0.7 \times 24\text{ V} - 1.2 \times 27\text{ V DC}$ With voltage tolerance and DC operated power consumption the following applies: At least smoothed double-pulse bridge rectification or a three-phase current rectifier is necessary
-------	--	--	--

Mounting position, AC- and DC operated



Dimensions




Dimensions



distance at side to earthed parts: 10 mm

Basic unit with auxiliary contact module

Characteristic curve



Squirrel-cage motor

Operating characteristics

Starting: from rest

Stopping: after attaining full running speed

Electrical characteristics

Make: up to $6 \times$ rated motor current

Break: up to $1 \times$ rated motor current

Utilization category

100 % AC-3

Typical applications

Compressors

Lifts

Mixers

Pumps

Escalators

Agitators

Fans

Conveyor belts

Centrifuges


Hinged flaps

Bucket-elevators

Air conditioning system

General drives in manufacturing and processing machines

Characteristic curve



Extreme switching duty
 Squirrel-cage motor
 Operating characteristics
 Inching, plugging, reversing
 Electrical characteristics
 Make: up to $6 \times$ rated motor current
 Break: up to $6 \times$ rated motor current
 Utilization category
 100 % AC-4
 Typical applications
 Printing presses
 Wire-drawing machines
 Centrifuges
 Special drives for manufacturing and processing machines

Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
 E-Mail: catalog@moeller.net, Internet: www.moeller.net, <http://catalog.moeller.net>
 Copyright 2006 by Moeller GmbH. HPL-C2007G V2.1