



PANDUIT PART #	WIRE RANGE		CRIMPING LENGTH	COMPRESSED AIR SUPPLY	WEIGHT
	AWG	[mm ²]			
CTFP-25	24-14	0.25-2.5	6 - 12 mm	5 bar / 72 psi	2.8kg / 6.2 lb
CTFP-40	24-12	0.25-4	6 -12 mm	5 bar / 72 psi	
CTFP-100	12-8	4-10	6 -12 mm	5 bar / 72 psi	

NOTES:

THE CTFP SERIES CRIMP TOOLS ARE PNEUMATIC FERRULE CRIMPING PRESSES INTENDED TO BE USED WITH LOOSE PIECE FERRULES.

GO TO PANDUIT.COM FOR A LIST OF PRODUCTS THAT ARE COMPATIBLE WITH THIS UNIT.

OVERALL APPROXIMATE DIMENSIONS:

CRIMPING UNIT: 2.75"H x 5.5"W x 7"L
 FOOT PEDAL: 5.5"H x 6"W x 8.5"L

						TITLE		PNEUMATIC FERRULE CRIMPING TOOL				
						CUSTOMER DRAWING						
						ITEM REVISION NAME		00090FPA/02				
						DATASET FILE NAME		00090FPA/01_DC/00A				
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:				
						.x ± .1 [2.54] .xxx ± .005 [.127]		N/A				
						.xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER:				
						THIRD ANGLE PROJECTION		00090FPA_DC				
02	10/24/2018	FCHE	TMR	JADE	CHANGE DRAWING NUMBER, CHANGE 20 GAGE TO 24 GAGE	041964						
01	8/30/2018	FCHE	TMR	FCHE	RELEASED	040535						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	
							FCHE	8/30/2018	TMR	N/A	B	



D10100DB/17