

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED TO PRODUCTION	03FEB2017	JPS	JLM
A1		REMOVE PRELIMINARY STATUS	03MAY2017	JPS	JLM
B		New P/N -8 and -9 ADDED	21SEP2017	CR	JLM
C		-8 Length Changed	09OCT2017	CR	JLM

- PARTS AND PROCESSES RoHS COMPLIANT PER TE CONNECTIVITY STANDARD TEC-138-702.
- 100% OPEN AND SHORT MISWIRE TEST.



250±5	IPX-20278-112R	BLACK	1.13 MM	2118651-9
200±3	IPX-20278-112R	BLACK	1.13 MM	2118651-8
90±2	IPX-20278-112R	BLACK	1.13 MM	2118651-7
90±2	IPX-20278-112R	GRAY	1.13 MM	2118651-6
70±2	IPX-20278-112R	BLACK	1.13 MM	2118651-5
40±2	IPX-20278-112R	BLACK	1.13 MM	2118651-4
75±2	IPX-20278-112R	BLACK	1.13 MM	2118651-3
30±2	IPX-20278-112R	BLACK	1.13 MM	2118651-2
140±3	IPX-20278-112R	BLACK	1.13 MM	2118651-1
A	CONNECTOR (2)	COLOR-CABLE (1)	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SCHOLZ 01APR2016														
DIMENSIONS: mm		CHK J. SCHOLZ 01APR2016														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. MOORE 01APR2016	NAME CABLE ASSEMBLY, COAX 1.13 MM DOUBLE ENDED, I-PEX PLUG 20278-112R-13													
<table border="0"> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±-</td> </tr> <tr> <td>2 PLC</td> <td>±-</td> </tr> <tr> <td>3 PLC</td> <td>±-</td> </tr> <tr> <td>4 PLC</td> <td>±-</td> </tr> <tr> <td>ANGLES</td> <td>±-</td> </tr> </table>		0 PLC	±-	1 PLC	±-	2 PLC	±-	3 PLC	±-	4 PLC	±-	ANGLES	±-	PRODUCT SPEC -	RESTRICTED TO -	
0 PLC	±-															
1 PLC	±-															
2 PLC	±-															
3 PLC	±-															
4 PLC	±-															
ANGLES	±-															
MATERIAL -		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2118651											
FINISH -		WEIGHT -	SCALE 5:1		SHEET 1 OF 1											
		CUSTOMER DRAWING	REV C													