




# CEJN SERIES 295 FOR PNEUMATIC APPLICATIONS




- High flow and completely leak proof thanks to our unique sealing design
- One-hand operation
- Brass construction for heavy duty installations
- Compact design
- High quality



### Specifications

Inlet pressure	6 bar (87.0 PSI)
Flow capacity	850 l/min (30.0 C.F.M.)
Max. working pressure	35 bar (508 PSI)
Min. burst pressure	140 bar (2000 PSI)
Temperature range	-30°C to + 100°C (-22°F to +212°F)
Nominal flow diameter	5.5 mm



INTERCHANGE:  
PCL Airflow  
Rectus 19


### Materials

Nipple	Steel, Hardened Zinc-plated
Coupling Front	Brass, Nickel-plated
Coupling Back	Brass, Nickel-plated
Locking Sleeve	Brass, Nickel-plated
6 Balls and Springs	Stainless Steel
Valve and Valve Seat	Brass
Seals	Nitrile

For actual size of nipple profile see page 5

## CEJN SERIES 295

## COUPLINGS



PART NO.	CONNECTION	LENGTH	DIA.	HEX A/F
<i>Hose Barb</i>				
10-295-1002	6 mm 1/4"	66.3	23.4	20
10-295-1003	8 mm 5/16"	68.3	23.4	20
10-295-1004	10mm 3/8"	67.3	23.4	20
10-295-1005	13mm 1/2"	66.3	23.4	20
<i>Male Thread</i>				
10-295-1152	1/4" BSPT	59.3	23.4	20
10-295-1154	3/8" BSPT	58.3	23.4	20
10-295-1155	1/2" BSPT	51.8	23.4	22
<i>Female Thread</i>				
10-295-1202	1/4" BSP	56.3	23.4	20