



Customer drawing



D-SUB TECHNICAL DATA

SHELL :	SPCC, 100u" Tin Over 50u" min nickel over 50u" min Copper
BODY :	PBT, UL 94V-0, Color:Black.
CONTACTS :	Copper Alloy. 30u"min gold over 50u" min nickel on mating area. 100u" min tin over 50u" min nickel on solder area
BOARDLOCK :	Copper Alloy, Tin Plated.
BRACKET :	Zinc Alloy. Nickel Plated.
ELECTRICAL :	Voltage rating :250 VAC(RMS) Max Current rating :3A Withstanding Voltage >1000 VAC(RMS) Insulation resistance >1000 M Ohms Contact resistance 25 mOhms max.

PRODUCT CODE

L 17H 2 2 2 2 1 2 0

RoHS Compliance

Spacing Between Ports:
2: F=19.05mm
G=31.60mm

Top Connector Type:
2=9-pos. Female


Bottom Connector Type:
2=9-pos. Female

Flange Mounting
Option:
0=Rear insert 4-40

Board Mounting Option:
2=Dual Arrowhead Boardlock

Front	Shell	Finish:
1= Tin	over	Nickel

Contact Finish:	2=30u" gold
-----------------	-------------

UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
TOLERANCES					
U.S.		METRIC			
.X +/-		0.50		DRAWN Peiza Liu 9/04/13	
.XX +/-		0.30		CHECKED Tony Tang 9/04/13	
.XXX +/-		0.20		CHECKED	
FRACTIONS					
ANGLES +/-		5°			
FOR MATERIALS AND FINISHES SEE NOTES					
REMOVE SHARP EDGES					
DIMENSIONS					
U.S.		INCHES			
METRIC		MM			
				DRAWING FILE :	
				ANGLE OF PROJECTION	
					

3	Amphenol
---	----------

Amphenol East Asia Limited

TITLE	Dual port connector, 17H series
--------------	---------------------------------

SIZE	DRAWING NO.	REV.
A4	C L17H2222120	3
SCALE	NONE	SHEET 1 OF 1