



1206 CHIP TYPE - Water Clear



)-2
2-3
)-4
-7

FEATURES



- Ultra-miniature
- Extremely low profile
- · Industrial standard footprint
- Wide viewing angle of 140°
- · Water clear optics
- · Moisture-proof packaging

DESCRIPTION

These surface mount lamps are designed to fit industry standard profile and footprint for ultraminiature chip type 1206. The low profile and 140° viewing angle make this chip type LED ideal for panel illumination, push-button backlighting and membrane switch applications.

ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise specified)					
Parameter	HER QTLP650C-2	Yellow QTLP650C-3	Green QTLP650C-4	AlGaAs Red QTLP650C-7	Units
Continuous Forward Current - I _F	30	20	30	30	mA
Peak Forward Current - I _F (f = 1.0 KHz, Duty Factor = 1/10)	160	160	160	160	mA
Reverse Voltage - V _R (I _R = 10 μA)	5	5	5	5	V
Power Dissipation - P _D	100	85	100	100	mW
Operating Temperature - T _{OPR}	-40 to +100			°C	
Storage Temperature - T _{STG}	-40 to +100			°C	
Lead Soldering Time - T _{SOL}					
Wave	260 for 5 sec			°C	
Reflow	260 for 10 sec				



1206 CHIP TYPE - Water Clear

HER	QTLP650C-2
YELLOW	QTLP650C-3
GREEN	QTLP650C-4
AlGaAs RED	QTLP650C-7

ELECTRICAL / OPTICAL CHARACTERISTICS (TA =25°C)					
Part Number	HER QTLP650C-2	Yellow QTLP650C-3	Green QTLP650C-4	AlGaAs Red QTLP650C-7	Condition
Luminous Intensity (mcd)					$I_F = 20mA$
Minimum	3.6	3.6	6.0	9.0	
Typical	6.0	6.0	10.0	15.0	
Forward Voltage (V)					$I_F = 20mA$
Maximum	2.8	2.8	2.8	2.4	
Typical	2.0	2.0	2.1	1.9	
Peak Wavelength (nm)	635	585	565	660	$I_F = 20mA$
Spectral Line Half Width (nm)	45	35	30	20	$I_F = 20mA$
Viewing Angle (°)	140	140	140	140	$I_F = 20mA$

TYPICAL PERFORMANCE CURVES




Fig. 1 Forward Current vs. Forward Voltage




Fig. 2 Relative Luminous Intensity vs.
DC Forward Current



1206 CHIP TYPE - Water Clear

HER QTLP650C-2
YELLOW QTLP650C-3
GREEN QTLP650C-4
AIGaAs RED QTLP650C-7




Fig. 3 Relative Intensity vs. Peak Wavelength




Fig. 4 Radiation Diagram





Fig. 5 Current Derating Curve




1206 CHIP TYPE - Water Clear

HER	QTLP650C-2
YELLOW	QTLP650C-3
GREEN	QTLP650C-4
AlGaAs RED	QTLP650C-7

RECOMMENDED PRINTED CIRCUIT BOARD PATTERN



RECOMMENDED IR REFLOW SOLDERING PROFILE





SURFACE MOUNT LED LAMP 1206 CHIP TYPE - Water Clear

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

© 2000 Fairchild Semiconductor Corporation