

6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION		QTY	UOM			FROM	TO	DESCRIPTION	COLOR
A,B	430250200	MicroFit 3.0 DR Rcpt 2Ckt		2	PC			A1	B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	430300040	MicroFit 3.0 F Crp Term Chn 30Au 18		4	PC			A2	B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
D	--	PAPER PRINTED PAPER WHITE		1	PC						




TABLE			
PART NUMBER	L1	L2	TITLE
2147552021	150±8	63REF	MICRO-FIT3.0 R-R 2 CIRCUIT 150MM Au
2147552022	300±10	138REF	MICRO-FIT3.0 R-R 2 CIRCUIT 300MMAu
2147552023	600±10	287REF	MICRO-FIT3.0 R-R 2 CIRCUIT 600MM Au

- NOTES
- Cable assembly must pass 100% continuity and polarity test.
 - Connector view shown is from mating side.
 - Label text must be 2mm max. in height with Arial font.
 - Label must be wrapped in Flag type.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
24/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex SEE TABLE						
 = 0	mm		NTS		EC NO: 629791 DRWN: ARAJU 2019/12/24 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18										
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)														
 = 0	ANGULAR TOL ± °														
 = 0	4 PLACES ±		±		INITIAL REVISION: DRWN: ARAJU 2019/12/24 APPR: RDESAI01 2020/01/18				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION		
 = 0	3 PLACES ±		±						2147552020		PSD	000	A		
 = 0	2 PLACES ±		±						2147552020		PSD	000	A		
 = 0	1 PLACE ±		±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
 = 0	0 PLACES ±		±						A4-SIZE		214755	SEE TABLE	GENERAL MARKET	1 OF 1	
 = 0															

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:03
-----------------	----	--------------	------------	----------