

PRELIMINARY




THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	PRELIMINARY	11SEP2019	T.S	E.I

1 MATERIAL AND FINISH
HOUSING : LIQUID CRYSTAL PLASTIC, BLACK
CONTACT : COPPER ALLOY, PLATING: CONTACT AREA SEE TABLE
SOLDERING AREA TIN


2. INSTRUCTION SHEET: 408-78171




0.38um GOLD	3	15	24.9	4	2-2336494-4
0.38um GOLD	2	10	19.9	3	2-2336494-3
TIN	3	15	24.9	4	2336494-4
TIN	2	10	19.9	3	2336494-3
CONTACT PLATING	D	DIM B	DIM A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 15MAY2019	TE Connectivity	
		CHK T.SHIMOYASU 15MAY2019		
		APVD F.IKEMATSU 15MAY2019	NAME HEADER ASSEMBLY, 180 DEGREE TYPE D2970 PUSH-IN TYPE, DYNAMIC FIELD INSTALLABLE CONNECTOR	
DIMENSIONS: mm		PRODUCT SPEC 108-140223		
		APPLICATION SPEC -		
		WEIGHT -		
MATERIAL -		CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779
FINISH -		SCALE 1:1	DRAWING NO C-2336494	RESTRICTED TO -
		SHEET 1	OF 2	REV 1

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 15MAY2019	 TE Connectivity			
DIMENSIONS: mm		CHK T.SHIMOYASU 15MAY2019	NAME HEADER ASSEMBLY, 180 DEGREE TYPE D2970 PUSH-IN TYPE, DYNAMIC FIELD INSTALLABLE CONNECTOR			
		APVD F.IKEMATSU 15MAY2019				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-140223	SIZE A3			
0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.5 3 PLC ±- 4 PLC ±- ANGLES ±5°		APPLICATION SPEC -				
MATERIAL -		WEIGHT -	DRAWING NO C-2336494		RESTRICTED TO -	
-			SCALE 5:1		SHEET 2 OF 2	
		CUSTOMER DRAWING			REV 1	