

Epson Stylus SX620FW

PRODUCT GUIDE



Ideal for the busy modern home, this sleek 4-in-1 with Wi-Fi delivers lab-quality photos and first-class documents at high speed. It also saves you money with a choice of economical individual ink cartridges.

Lose the wires and print, scan, copy and fax from anywhere in your home with this 38 ppm*1 4-in-1 that includes the latest 802.11n wireless technology*2.

View and print photos quickly and easily using the large 6.3 cm LCD screen, and print direct from memory cards, USB keys and PictBridge-enabled digital cameras.

It's simple to make multi-page scans and copies and send multi-page faxes with the automatic document feeder.

And with a choice of individual ink cartridges, you can save money as you only need to only replace the colour used.

WHAT'S IN THE BOX

- Epson Stylus SX620FW
- 4 individual ink cartridges
- Software CD
- Basic operation guide
- 'Start Here' guide
- Wi-Fi/Network set-up guide
- Control panel icon sticker
- Warranty document
- Power cable
- Phone cable

FOR THE BEST RESULTS ALWAYS USE GENUINE EPSON INK AND PAPER.

Epson DURABrite Ultra Ink is perfect for all your home printing because it gives you enduring Epson quality on a wide range of media.

- Outstanding text documents and lab-quality photos
- Instant-drying prints are water, smudge, highlighter and fade resistant
- Resin-coated pigment technology works perfectly on a range of papers
- Lab-quality glossy photos last over 200 years in a photo album*1



EPSON[®]
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

<p>PRINT TECHNOLOGY Printing method Nozzle configuration Droplet size Ink system</p>	<p>4-colour inkjet printer, Epson Micro Piezo™ print head 384 nozzles black / 128 nozzles, each colour (cyan, magenta, yellow) 2 pl (minimum) with Variable-sized Droplet Technology Epson DURABrite Ultra Ink</p>
<p>PRINT RESOLUTION</p>	<p>Up to 5760x1440 optimised dpi on suitable media using RPM (Resolution Performance Management)</p>
<p>PRINT SPEED Black text A4 Colour text A4 Photo 10x15 cm</p>	<p>Up to 38 ppm*1 Up to 38 ppm*1 Approx. 20 secs*1</p>
<p>SCANNING Scan resolution Technology Sensor type Speed</p>	<p>2400x2400 dpi A4 flatbed colour image scanner CIS Black A4: 300 dpi 1.1 msec/line, 600 dpi 1.9 msec/line Colour A4: 300 dpi 3.0 msec/line, 600 dpi 5.8 msec/line</p>
<p>LCD AND MEMORY CARDS LCD screen Supported memory cards</p>	<p>6.3 cm colour Compact Flash, MicroDrive, Memory Stick, Memory Stick Duo^{®3}, MagicGate Memory Stick, MagicGate Memory Stick Duo^{®3}, Memory Stick PRO, Memory Stick PRO Duo^{®3}, Memory Stick PRO-HG Duo^{®3}, Memory Stick Micro M2^{®3}, SD, SDHC, MiniSD^{®3}, MiniSDHC^{®3}, MicroSD^{®3}, MicroSDHC^{®3}, Multi Media Card, MMCplus, MMCmobile^{®3}, MMCmicro^{®3}, xD-Picture card, xD-Picture card Type-M, xD-Picture card Type-M+, D-Picture card Type-H</p>
<p>INTERFACE USB Wi-Fi Ethernet Other</p>	<p>Hi-Speed USB – compatible with USB 2.0 specification Wireless LAN IEEE 802.11b/g/n Wired LAN IEEE 802.3 (10BASE-TX, 10BASE-T) PictBridge</p>
<p>WIRELESS SECURITY</p>	<p>WEP – 64bit WEP – 128bit WPA – PSK (TKIP) – compliant with WPA2 WPA – PSK (AES) – compliant with WPA2</p>
<p>FAX FUNCTION Type of fax Fax speed Fax resolution Error correction mode Fax speed dials (max) Page memory Fax transmission speed</p>	<p>Walk-up Black and white and colour fax capability Up to 33.6 kbps Standard (200x100), Fine (200x200), Photo (200x200 with error diffusion) CCITU/ITU Group3 fax with Error Correction Mode 60 names and numbers Up to 180 pages (ITU-T No.1 chart) Approx. 3 sec per page</p>
<p>ADF FUNCTION Maximum document size Paper type Paper thickness Maximum number of pages</p>	<p>A4 Plain paper only 60-95 g/m² 30 (based on Xerox-P 64 g/m²)</p>
<p>PAPER HANDLING Capacity Media size Print margin</p>	<p>Input: 250 sheets A4 plain paper (75 g/m²) A4, Letter, Legal, 20x25 cm, 13x20 cm, 13x18 cm, 16.9 wide size, 10x15 cm, 9x13 cm, A5, A6, B5, User Defined, Envelopes: No. 10, DL, C6 0 mm top, left, right, bottom via custom settings in printer driver⁴</p>
<p>INK CARTRIDGES Black series Apple series</p>	<p>4 individual ink cartridges Black Cyan Magenta Yellow T1301 T1302 T1303 T1304 T1291 T1292 T1293 T1294</p>
<p>ELECTRICAL SPECIFICATION Power consumption Voltage</p>	<p>Approx. 16W (standalone copying, ISO10561 Letter Pattern) Approx. 3.8W (sleep mode) ENERGY STAR[®] qualified All-in-One AC 220-240V</p>
<p>OPERATING SYSTEMS</p>	<p>Windows XP/XP-x64/Vista/Win 7, Mac OS 10.4.11 or later</p>
<p>WARRANTY</p>	<p>1 year standard warranty Optional extension to 3 years subject to availability</p>
<p>GENERAL Dimensions (WxDxH) Weight Noise level</p>	<p>446x360x221 mm 7.6 kg (excluding ink cartridges and power cable) 5.3 B(A) (according to ISO7779 pattern with Epson Premium Glossy Photo Paper/Photo RPM mode) 39 dB(A) (according to ISO9296)</p>
<p>SOFTWARE</p>	<p>Epson Easy Photo Print, Epson Event Manager, EpsonNet Setup, Epson Fax Utility, Epson Web Support, ABBYY FineReader[®] 9.0 Sprint (PC), ABBYY FineReader[®] 8.0 Sprint (Mac)</p>

INK CARTRIDGE COMPATIBILITY



XL

- T1301
- T1302
- T1303
- T1304
- T1306



L

- T1291
- T1292
- T1293
- T1294
- T1295

RECOMMENDED PAPER

Epson's Micro Piezo™ inkjet technology gives great results on a wide range of paper types, giving you the flexibility to print whatever you want. And Epson produces a range of paper to help you do this, from A4 inkjet paper through to glossy photo paper in a variety of sizes.



★★★★☆

PHOTO PAPER

190 g/m²



★★★★☆

GLOSSY PHOTO PAPER

225 g/m²



★★★★★

PREMIUM GLOSSY PHOTO PAPER

255 g/m²

¹ For more information please visit www.epson-europe.com
² When used with other 802.11n products. Wi-Fi speed may vary depending on physical environment.
³ Adaptor required (not supplied in box).
⁴ Otherwise 3 mm top, left, right, bottom.



For more information please contact
 Telephone: 0871 222 6702 (UK)*
 01 436 7742 (Republic of Ireland)
 E-mail: enquiries@epson.co.uk
 Chat: etalk.epson-europe.com
 Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

* Calls cost 10 pence per minute from a standard BT landline.
 Calls from other networks and mobiles may vary.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
 Product information is subject to change without prior notice.

