

Customer Information Sheet

DRAWING No.: M20-784XXXX

SHEET 3 OF 3


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



SPECIFICATION:

MATERIAL:

MOULDING - NYLON 6T UL94V-0, BLACK
CONTACTS - PHOSPHOR BRONZE

FINISH:

42 - GOLD ON CONTACT AREA, 100% TIN ON TAILS
46 - 100% TIN

ELECTRICAL:

CURRENT RATING - 3A
VOLTAGE PROOF - 600V AC FOR 1 MINUTE
CONTACT RESISTANCE - 20 MILLIOHMS MAX
INSULATION RESISTANCE - 1,000 MEGOHMS MIN


ENVIRONMENTAL:

TEMPERATURE RANGE - -40° TO +105°

PACKING:

TUBE

FOR COMPLETE SPECIFICATION SEE COMPONENT SPECIFICATION C001XX (LATEST ISSUE)



ORDER CODE:

M20-784XXXX

No. OF WAYS

02 TO 40

FINISH:

42 - SELECTIVE GOLD + 100% TIN
46 - 100% TIN

NOTES:

1. THIS CONNECTOR CAN ALSO BE USED FOR TOP ENTRY.

RA	3	12.11.08	10203
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: JM BROOKES			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:
2.54mm PITCH SIL PC TAIL
DUAL ENTRY SOCKET ASSY

DRAWING NUMBER:
M20-784XXXX

SHT
3
OF
3