



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-016412	12OCT2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB


D



2320925-2
(BLUE TPA)
KEY B
SCALE 2:1




2320925-3
(PURPLE TPA)
KEY C
SCALE 2:1





2320925-4
(ORANGE TPA)
KEY D
SCALE 2:1

C



B



SECTION A-A
SCALE 3:1


- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: GREEN
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
- A. 2292802-1 SMOOTH WIRE EXIT
 - B. 2292802-2 NC20/NWI7 CONDUIT WIRE EXIT
 - C. 2292802-3 NC16/NWI3 CONDUIT WIRE EXIT
- 90° EXIT:
- D. 2302495-1 SMOOTH WIRE EXIT
 - E. 2302495-2 NC20/NWI7 CONDUIT WIRE EXIT
 - F. 2302495-3 NC16/NWI3 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320918-X.

D


C

B

A



SCALE 2:1



SCALE 2:1

D	ORANGE	2320925-4
C	PURPLE	2320925-3
B	BLUE	2320925-2
A	TAN	2320925-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MCNEAL 12OCT2018	TE Connectivity		
		CHK R BALTER 12OCT2018			
		APVD R BALTER 12OCT2018	NAME		
		PRODUCT SPEC			
DIMENSIONS:		108-2184	PLUG ASSEMBLY, 12 POSITION, STD DIA SEAL HIGH TEMP, AMPSEAL 16		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		114-13065			
mm		WEIGHT 20±1g	SIZE	CAGE CODE	DRAWING NO
		Customer Drawing	A20779	C-2320925	RESTRICTED TO
			SCALE 1:1	SHEET 1	REV A1