



- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: LT GRAY



4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT
A. 2292863-1 SMOOTH WIRE EXIT
B. 2292863-2 NCI6/NWI3 CONDUIT WIRE EXIT
C. 2292863-3 NCI2/NWI0 CONDUIT WIRE EXIT

90° EXIT
D. 2302484-1 SMOOTH WIRE EXIT
E. 2302484-2 NCI6/NWI3 CONDUIT WIRE EXIT
F. 2302484-3 NCI2/NWI0 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1
7. MATING CONNECTOR: 2320935-X.



C	PURPLE	2320929-3
B	BLUE	2320929-2
A	TAN	2320929-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ±-
	1 PLC ±-
	2 PLC ±0.30
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
-	-
-	-

DWN	J. MCNEAL	05MAR2018
CHK	R. BALTER	05MAR2018
APVD	R. BALTER	05MAR2018
PRODUCT SPEC	108-2184	
APPLICATION SPEC	114-13065	
WEIGHT	15.5	
Customer Drawing		

TE Connectivity

NAME
CAP ASSEMBLY, 6 POSITION,
REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	-	C-2320929	-
SCALE 2:1		SHEET 1 OF 1	REV A1