





注記 NOTE

- 1. ウエハーのそりは、長さ25.4に対して0.24MAX.
CHAMBER MUST BE 0.24 MAX. PER 25.4
- 2. ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT.

49.72	45.72	10-63-1099	5285-09A	9
44.64	40.64	↑ -1089	↑ -08A	8
39.56	35.56	-1079	-07A	7
34.48	30.48	-1069	-06A	6
29.4	25.4	-1059	-05A	5
24.32	20.32	-1049	-04A	4
19.24	15.24	↓ -1039	↓ -03A	3
14.16	10.16	10-63-1029	5285-02A	2
B	A	EDP NO.	ENG. NO.	NO. OF CKT.



REVISED EC NO: J2007-2743 DRWN:TYAMADA01 2007/04/10 CHKD:THARUYAMA 2007/04/10 APPR:NUKITA 2007/04/12	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	H.HIRAMOTO	1998/01/23	TITLE KK 5.08/10.16 WAFER ASSY WITH LOCK				
		10 OVER 30 UNDER	±0.25	CHECKED BY	DATE					
		30 OVER	±0.3	H.HIRAMOTO	1996/03/14	MOLEX INCORPORATED				
		APPROVED BY	DATE							
		M.FUKUSHIMA	1996/03/14	DOCUMENT NO.						
	ANGULAR ±3 °		MATERIAL NO.						SD-5285-001	
REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				