





| REVISIONS | | | | |
|-----------|------|---------------|-----------|-------|
| P. | LTR. | DESCRIPTION | DATE | APVD |
| A | | FIRST RELEASE | 03JUL2019 | SZ SZ |
| A1 | | ECO-20-010950 | 05AUG2020 | SZ SZ |

NOTES, UNLESS OTHERWISE SPECIFIED

1. MATERIAL:
 HOUSING - THERMOPLASTIC, GLASS PREINFORCED, COLOR, BLACK, UL 94V-0
 CONTACTS - COPPER ALLOY.

2. FINISH:
 MATING AREA - NOBLE METAL OVERALL NICKEL.
 SOLDER TAIL - MATTE TIN OVERALL NICKEL.

3. MARK P/N AND DATA CODE IN APPROX. AREA AS SHOWN.



| | | | | |
|--|--------------|---------------------------|---|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN: SEAN_ZHANG 03SEP2018 | PART NUMBER 2343428-1 | |
| DIMENSIONS: mm | | CHK: - | TE Connectivity NAME HDCE PLUS, RIGHT ANGLE 2X6 POWER, 2X7 SIGNAL | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD: - | | |
| 0 PLC ±0.50 | 1 PLC ±0.25 | PRODUCT SPEC | SIZE CAGE CODE DRAWING NO. RESTRICTED TO | |
| 2 PLC ±0.25 | 3 PLC ±0.25 | APPLICATION SPEC | A100779C=2343428 | |
| 4 PLC ±0.25 | ANGLES ±0.25 | WEIGHT | SCALE 2:1 SHEET 1 OF 2 REV A1 | |
| MATERIAL | FINISH | CUSTOMER DRAWING | | |

