

## Customer Information Sheet


NOT TO SCALE DRAWING No.: M80-5CIXXXXBI SHEET 2 OF 2 THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm





## NOTES:


- I. SUPPLIED AS A KIT OF PARTS, CONNECTORS SHOWN ASSEMBLED FOR INFORMATION PURPOSES ONLY.
- 2. CONNECTORS WITH JACKSCREWS ASSEMBLED, SLOTTED NUTS AND CONTACTS WILL BE SUPPLIED LOOSE IN A BAG. BACKSHELLS WILL BE INDIVIDUALLY BAGGED. KITS WILL BE BULK PACKED INTO BOXES
- 3. FOR EXTRA CONTACTS, USE PART No: M80-1950005 FOR M80-5CIXX05BI
- 4. FOR M80-5CIXXO5BI RECOMMENDED WIRE TYPE = BS 3G 210 TYPE A, PTFE INSULATED 24-28 AWG. MAX INSULATION DIAMETER = Ø1.10mm.STRIP WIRE BY 2.00mm.
- 5. RECOMMENDED HAND CRIMP TOOL FOR ALL CONTACTS = M22520/2-01 WITH POSITIONER Z80-193
- 6. CONTACT INSERTION AND EXTRACTION TOOL = Z80-280.
- 7. INSTRUCTION SHEETS ARE AVAILABLE.











14.03.11 DATE C/NOTE APPROVED: S.BENNETT CHECKED: S.FLOWER DRAWN: S.FLOWER CUSTOMER REF.:

EXAMPLE ORDER CODE: CONNECTOR WITH 20 SMALL BORE CONTACTS, ALL OVER GOLD CONTACT.

M80-5C12005B1

## HARWIN

HARWIN Asia HARWIN Europe (UK) HARWIN USA TEL: 603 893 5376 TEL: 023 9231 4545 TEL: +65 6 779 4909 FAX: 603 893 5396 FAX: 023 9231 4590 FAX: +65 6 779 3868 mis@harwin.com.sg mis@harwin.com mis@harwin.co.uk

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TEMBERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

X. = ±1mm  $X.X = \pm 0.25 mm$  $X.XX = \pm 0.10$ mm X.XXX = ±0.01mm UNLESS STATED

TOLERANCES

MATERIAL:

S/AREA:

SEE ABOVE FINISH: SEE ABOVE

mm 2

TITLE: DATAMATE J-TEK DIL MALE CRIMP (SMALL BORE) ASSY WITH METAL BACKSHELL

ASSEMBLY DRG:

DRAWING NUMBER:

M80-5CIXXXXBI