


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-09-006452	30/03/09	AM	JS



- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - MATERIAL: BODY - BRASS
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838229-0	1.5mmsq-2.5mmsq	6.4x0.8mm STANDARD ENTRY	BLUE PIGGY BACK TERMINAL (INSULATED)	1500	500	6.80	6.35	23.00	4.90	11.00	0.40	0.80	1.5mmsq-2.5mmsq	6.4 X 0.8	BLUE PIGGY BACK TERMINAL (INSULATED)	2-1838229-0
1-1838229-0	16-14 (AWG)			1750	50								16-14(AWG)			1-1838229-0
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	B (±0.30)	b (±0.20)	L (±1.50)	D (±0.50)	E (±0.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	SIZE (mm)	DESCRIPTION	PART No
DIMENSIONS																

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± 0.015
4 PLC ± -
ANGLES ± -
FINISH -

FINISH -

DWN 25AUG05 K.Raghunandan
CHK 03/04/07 S. Parlow
APVD 03/04/07 F. Wheeler-King
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -


CUSTOMER DRAWING

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME EURO-CRIMP INSULATED BLUE PIGGY BACK TERMINAL
1.5mmsq-2.5mmsq / 16-14 AWG RANGE

SIZE A2 CAGE CODE 00779 DRAWING NO C=1838229 RESTRICTED TO -

SCALE NTS SHEET 1 OF 2 REV B



- LABEL NOTES:

1. PERFORATED LINE:

DOTTED LINE TO BE ALIGNED WITH OPENING EDGE & FOLDED TO LEFT SIDE OF BOX.

2. LOGO:

USE LATEST REVISION OF TYCO COMPANY LOGO.

3. LINE1:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 1.

4. PART NUMBER:

FOR 1--0 & 2--0 USE TYCO PART NUMBER.
1--0 = 1-1838229-0
2--0 = 2-1838229-0

5. LINE 2:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 2.

6. LINE 3:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 3.

7. QTY:

SEE SHEET 1, USE NUMBER FROM THE COLUMN QTY.

8. EAN BARCODE.

USE LATEST TYCO BARCODE SUPPLIED.
1--0 = TYCO BARCODE
2--0 = TYCO BARCODE

9. UL:

WHERE APPLICABLE USE UL LOGO, SEE SHEET 1.

10. PRODUCT PICTURE:

A PRODUCT PICTURE IS REQUIRED.
- BOX NOTES:

1. EURO SLOT:

TO BE POSITIONED TO CENTRE ON FRONT COVER.

2. BOX HINGE:

FRONT COVER TO BE HINGED ON RIGHT SIDE.

3. SPECIFICATION:

COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES.

4. LABEL:

CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE.
- PACK SPECIFICATION:

1. CLEAR PLASTIC BOX:


PART NUMBER 1--0 TO BE PACKED 50 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

2. CLEAR PLASTIC BAG:

PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR 500 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 3 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

3. INNER CARTON LABEL:

LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 1500 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Raghunandan		25AUG05		 Tyco Electronics Corporation Bideford, UK, EX39 4HE					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK S. Parlow		03/04/07					
	0 PLC	±	0.5	APVD F. Wheeler-King		03/04/07					
	1 PLC	±	0.2	PRODUCT SPEC		NAME					
	2 PLC	±	0.1	—		EURO-CRIMP INSULATED BLUE PIGGY BACK TERMINAL					
	3 PLC	±	0.015	APPLICATION SPEC		1.5mmsq-2.5mmsq / 16-14 AWG RANGE					
	4 PLC	±	—	—		SIZE					
MATERIAL		FINISH		WEIGHT		CAGE CODE		DRAWING NO		RESTRICTED TO	
—		—		—		A2		00779		C=1838229	
CUSTOMER DRAWING								SCALE		SHEET	
								NTS		2 OF 2	
										REV B	