




Customer drawing



Positions	A	B	D	E	F
15	30.81	24.99	16.33	2.29	19.20
26	39.20	33.30	24.70	2.29	27.70
44	53.05	47.04	38.40	2.29	41.10
62	69.40	63.50	54.80	2.41	57.30




78 Positions

SYM	ECN	DESCRIPTION	DATE	APPROVAL
1	HK--	First Release Drawing	10/18/17	IP
2	HK--	Adding pin assignment	10/20/17	IP

SHELL :	Steel, 100u" min Tin over 50u" min nickel over 50u" min Copper
BODY :	Glass-Filled Thermoplastic PBT, UL94V-0, color black
CONTACTS :	Copper alloy 30u" Gold over 50u" min nickel on mating area 100u" min tin over 50u" min nickel on solder area
ELECTRICAL :	Voltage rating 250 V Rms Current Rating 3 AMP Withstanding Voltage >500 V Rms Insulation resistance >1000 M Ohms Contact resistance 20 mOhms max
MARKING :	Amphenol-...(Series No.) Commercial reference Manufacturing date

L 77 HD X XX S C309



UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE	Amphenol
U.S.	METRIC	DRAWN	Simon	10/10/77	
.X +/-	0.50	CHECKED	Tony Tang	10/10/77	
.XX +/-	0.30	CHECKED			
.XXX +/-	0.20				
FRACTIONS +/-					
ANGLES +/-	5°				
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :			
REMOVE SHARP EDGES		ANGLE OF PROJECTION			
DIMENSIONS					
U.S.	INCHES				
METRIC	MM				
		SIZE			REV
		DRAWING NO.			
		A4 L77HDXSC309			2
		SCALE		NONE	SHEET 1 OF 1