







LOC		DIST		REVISONS			
GP	00	P	LYR	DESCRIPTION		DATE	DWN
							APVD
				C3 REVISED PER ECO-11-005027		20APR11 RK	HMR



SCALE 4:1




3.00 TYP
TAIL LENGTH




- 1 MATERIAL: 0.25 THICK COPPER ALLOY.
- 2 FINISH: TIN. NONPLATED EDGES PERMISSIBLE.
3. SFP MSA COMPATIBLE.
- 4 PADS AND VIAS CHASSIS GROUND.
- 5 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
6. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED= 1.45
DOUBLE SIDED= 3.00


AS SHOWN	1489669-1
DESCRIPTION	PART NUMBER



DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN M. E. SHIRK 02AUG01		TE Connectivity				
mm		0 PLC	±	CHK J. KOPPENHEFFER 31MAY02	NAME	CAGE ASSEMBLY, 11 PRESS FIT, SFP				
		1 PLC	±0.10	APVD M. WALMSLEY 31MAY02						
	ANGLES	2 PLC	±	PRODUCT SPEC		SIZE CAGE CODE DRAWING NO				
		3 PLC	±	APPLICATION SPEC		A100779C-1489669				
		4 PLC	±	114-13120		RESTRICTED TO				
		MATERIAL		FINISH		WEIGHT		-		
		- 1		- 2		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 3 REV C3		

LOC		DIST		REVISIONS				
GP	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
		-	-	SEE SHEET 1	-	-	-	



SCALE 8:1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN M. E. SHIRK 02AUG01		 TE Connectivity									
mm				CHK J. KOPPENHEFFER 31MAY02											
		0 PLC ±		APVD M. WALMSLEY 31MAY02		NAME		CAGE ASSEMBLY, 11 PRESS FIT, SFP -							
		1 PLC ±0.10		PRODUCT SPEC											
		2 PLC ±		108-1950											
		3 PLC ±		APPLICATION SPEC											
4 PLC ±				114-13120		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A 100779		C=1489669				-			
-		-		-		CUSTOMER DRAWING		SCALE		5:1		SHEET 2 OF 3		REV C3	



RECOMMENDED PCB LAYOUT
SCALE 8:1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN M. E. SHIRK 02AUG01 CHK J. KOPPENHEFFER 31MAY02 APVD M. WALMSLEY 31MAY02		NAME	
mm		9 PLC ±		PRODUCT SPEC		CAGE ASSEMBLY, 11 PRESS FIT, SFP	
		2 PLC ±0.10		108-1950		SIZE CAGE CODE DRAWING NO	
		3 PLC ±		APPLICATION SPEC		RESTRICTED TO	
		4 PLC ±		114-13120		A 100779 C=1489669	
MATERIAL	-	FINISH	-	WEIGHT		CUSTOMER DRAWING	
				SCALE 5:1		SHEET 3 OF 3	
						REV C3	