


ISS.	AMEND	DATE
1	ISSUED	11/02/21



ITEM	DESCRIPTION	MATERIAL	FINISH	QTY
1	BODY (FRONT)	ZINC ALLOY	NICKEL PLATE	1
2	BODY (REAR)	ZINC ALLOY	NICKEL PLATE	1
3	CONTACTS	BRASS	SILVER PLATE	3
4	EARTH CONTACT	STEEL	TIN PLATE	1
5	GROMMET	PVC	BLACK	1
6	TOP SCREW	STEEL	NICKEL PLATE	1
7	SCREW	STEEL	NICKEL PLATE	2
8	INSERT	PBT	GREY	1
9	BUTTON	ZINC ALLOY	NICKEL PLATE	1
10	SPRING	SPRING STEEL	BLACK	1
11	CASING	BRASS	NICKEL PLATE	1

NOTE

Contact Resistance: $\approx 5\text{m}\Omega$
Insulation Resistance: $\approx 5000\text{M}\Omega$
Withstand Voltage: 1400V
Durability (Mating / Unmating): ≈ 2000
Insertion and Extraction Force: 10-80N

RoHS
COMPLIANT

TOLERANCE

NO DEC. PLACE $\pm$
1 DEC. PLACE $\pm$
2 DEC. PLACE $\pm$
HOLE $\varnothing \pm$
ANGLES $\pm$
UNLESS
OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmetherpe Avenue, Holmetherpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2021

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DRAWN: T.J.O.

APPROVED: D.P.J.

3rd ANGLE PROJECTION:

TITLE: AUDIO PLUG 3APF/MRA 3 POLE FEMALE

DRWG. No. **FC60953N**

FORM: A4DRWGH

DO NOT SCALE