

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

— , — *

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

AJ

16

	F
--	---

LTR

DESCRIPTION

DATE _____

DWN

APVD


M1

REVISÉ PER ECO-11-005030

11 MAR 11

RK

HMR



1 BRASS PER QQ-B-627.


△ 2 SILVER PLATE PER QQ-S-365, $5.08\mu\text{m}$ [.000200]
MINIMUM THICK.

3 NICKEL PLATE PER QQ-N-290, $2.54\mu\text{m}$ [.000100]
MINIMUM THICK.

△ 4 $\phi 0.79 \pm 0.08 [.031 \pm .003]$ (3 HOLES) 120° APART.

△ 5 GOLD PLATE PER MIL-G-45204, $0.51\mu\text{m}$ [.000020]
MINIMUM THICK.

2.77[.109]	15.82[.623]	—			2-329631-2
2.77[.109]	15.82[.623]	—			2-329631-0
2.77[.109]	15.82[.623]	—			1-329631-9
2.39±0.15[.094±.006]	14.10±0.25[.555±.010]				1-329631-7
2.39±0.15[.094±.006]	14.10±0.25[.555±.010]	—			1-329631-2
2.39±0.15[.094±.006]	14.10±0.25[.555±.010]	—			329631
B	A	HOLES	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. ALSEDEK 16MAY90		TE Connectivity											
		CHK R.E. RUTH 06SEP90													
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. PHILLIPS 20SEP90		NAME JAM NUT —									
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —											
MATERIAL 		FINISH  & 		APPLICATION SPEC —		SIZE A3		CAGE CODE 00779		DRAWING NO C-329631		RESTRICTED TO —			
				WEIGHT [.030 oz]											
CUSTOMER DRAWING										SCALE 4:1		SHEET 1 OF 1		REV M1	