






LOC		DIST		REVISIONS					
FT		O		P	LTR	DESCRIPTION	DATE	DWN	APVD
			L			REVISED PER ECO-12-015521	28SEP12	KH	MZ



RECOMMENDED PANEL CUTOUT

DETAIL A



DETAIL B

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT THIRTY-SEVEN (37) MULTIMATE SOCKET CONTACTS.
- 3 NO 4 FASTENER RECOMMENDED FOR MOUNTING.
- 4 NYLON 6/6, NATURAL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE 5	STANDARD	NO	3.81 [.150] DIA HOLE	A	4 206306-8
	SMALL PACK	NO	3.81 [.150] DIA HOLE	A	206306-6
	STANDARD	NO	4-40 THREADED INSERT	A	206306-5
	STANDARD	YES	-	B	206306-4
	STANDARD	YES	3.81 [.150] DIA HOLE	A	206306-3
	STANDARD	NO	-	B	206306-2
	STANDARD	NO	3.81 [.150] DIA HOLE	A	206306-1
	PACKAGING	PERIPHERAL SEAL	C	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ 07/26/93	TE Connectivity		
DIMENSIONS: MM [INCHES]		CHK R.STONE 08/11/93			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD A.FRANTUM 08/13/93	NAME		
		PRODUCT SPEC	108-10024		
		APPLICATION SPEC	-		
MATERIAL HOUSING: NYLON, BLACK INSERT: BRASS	FINISH -	WEIGHT -	A1 00779 C=206306		
		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV L		