

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2157601006

Status:

Active

Overview:

Micro-Fit+ Connector System

Description:

Micro-Fit+ Right-Angle Header, 3.00mm Pitch, Single Row, 6 Circuits, Matte Tin (Sn) Plating, UL 94V-0, Glow-Wire Capable, Black

Documents:

Drawing (PDF)

Product Specification 2064600000-PS-000 (PDF)

Test Summary 2157590005-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

215760

Power, Wire-to-Board

Micro-Fit+ Connector System

Micro-Fit+

193264935727

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Temperature Range - Operating

Termination Interface: Style

No

6

6

Black

25

No

Yes

Yes

Yes

High Copper Alloy

Matte Tin

Liquid Crystal Polymer

1.054/g

1

Right Angle

3.18mm

1.57mm

Tray

3.00mm

3.00mm

Yes

Yes

Yes

-40° to +105°C

Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

13.0A

600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

Test Summary

2064600000-PS-000

2157600002-PK-000, 2157600003-SD-000

2157590005-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

215760 Series

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION