




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT -

ALL RIGHTS RESERVED.


REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.



SCALE 3:1



SOLDER DETAIL
SCALE 10:1




EXAMPLE SOLDER JOINT

NOTES:


- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 OF 2
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S3	APPLICATION SPECIFICATION NUMBER ADDED	24JUL2013	KJK	RP

1 PARTNUMBER VAC. TAPE.	3 PARTNUMBER	NR.OF POS. "n"	"A"	"B" MAX.
7-188275-4	0-188275-4	4	3,81	7,1
7-188275-6	0-188275-6	6	6,35	9,7
7-188275-8	0-188275-8	8	8,89	12,2
8-188275-0	1-188275-0	10	11,43	14,7
8-188275-2	1-188275-2	12	13,97	17,3
8-188275-4	1-188275-4	14	16,51	19,8
8-188275-6	1-188275-6	16	19,05	22,4
8-188275-8	1-188275-8	18	21,59	24,9
9-188275-0	2-188275-0	20	24,13	27,5




ACCORDING EIA-481/DIN IEC 286



DETAIL X
SCALE 1:1

POLARIZATION-SLOT
ON THIS SIDE.

3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL
ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR



RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW


THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-	1 PLC ±-
2 PLC ±-	3 PLC ±-
4 PLC ±-	ANGLES ±-
MATERIAL SEE TABLE	FINISH SEE TABLE

DWN M.GOSSELINK	-
CHK -	-
APVD -	-
PRODUCT SPEC 108-19052	-
APPLICATION SPEC 114-13318	-
WEIGHT -	-
CUSTOMER DRAWING	



TE Connectivity		NAME	
CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, Micro-MaTch		RESTRICTED TO	
SIZE A3	CAGE CODE 00779	DRAWING NO C-188275	REV S3
SCALE 5:1		SHEET 1 OF 2	

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
COPYRIGHT - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
H	-			SEE SHEET 1		



7-188275-4	7-188275-6	7-188275-8	8-188275-0
4 POSITION	6 POSITION	8 POSITION	10 POSITION
0-188275-4	0-188275-6	0-188275-8	1-188275-0



8-188275-2	8-188275-4	8-188275-6	8-188275-8	9-188275-0
12 POSITION	14 POSITION	16 POSITION	18 POSITION	20 POSITION
1-188275-2	1-188275-4	1-188275-6	1-188275-8	2-188275-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.1

2 PLC ±0.05

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

DWN
M. GOSSELINK

CHK -

APVD -

PRODUCT SPEC
108-19052

APPLICATION SPEC
114-13318

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, Micro-MaTch

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-188275

RESTRICTED TO
-

SCALE
1:1

SHEET
2

OF
2

REV
S3