

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2157603006

Status:

Active

Overview:

Micro-Fit+ Connector System

Description:

Micro-Fit+ Right-Angle Header, 3.00mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, UL 94V-0, Glow-Wire Capable, Black

Documents:

Drawing (PDF)

Product Specification 2064600000-PS-000 (PDF)

Test Summary 2157590005-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

215760

Power, Wire-to-Board

Micro-Fit+ Connector System

Micro-Fit+

193264937318

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to Mating Part

Polarized to PCB

Shrouded

Temperature Range - Operating

Termination Interface: Style

No

6

6

Black

200

No

Yes

Yes

Yes

High Copper Alloy

Gold

Liquid Crystal Polymer

1.054/g

1

Right Angle

3.18mm

1.57mm

Tray

3.00mm

3.00mm

0.762µm

Yes

Yes

Yes

-40° to +105°C

Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

12.5A

600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

Test Summary

2064600000-PS-000

2157600002-PK-000, 2157600003-SD-000

2157590005-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215760 Series

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION