







PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR MATERIAL: PBT
FLAMMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES


ENVIRONMENTAL
OPERATING TEMPERATURE: -40 °C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.5 A
WORKING VOLTAGE: 120 VAC
INSULATION RESISTANCE: >500 MΩ
WITHSTANDING VOLTAGE: 1 000 VAC/MIN
CONTACT RESISTANCE: 20 mΩ MAX

STANDARD
CERTIFIED: E324776

SOLDERING
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
TRAY

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	 WÜRTH ELEKTRONIK		
G								
F	18-JUL-14	CHARACTERISTICS	AS					
E	03-JAN-14	UL & TEMP UPDATE	QL					
D	28-AUG-13	DWG UPDATE	QL					
C	28-MAY-10	DIM. 1.9MM	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: HORIZONTAL SHIELDED 2 x 4 STACKED PORT WITH EMI PANEL FINGER 8P8C MODULAR JACK TAB UP & DOWN		SIZE
B	06-OCT-09	UL STANDARD	JP		SCALE:			
A	28-AUG-08	PDF	CH		SHEET: 1/1			
REV	DATE	FILE	BY		DRAW:	WERI PART NO: 615 064 243 321		

D

A4