



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANCON.



| PART NUMBER * | No. OF CIRCUITS | DIM "A" IN. (MM) | WT./100 PCS. LBS. (GRAMS) |
|---------------|-----------------|------------------|---------------------------|
| EC100F-2 | 2 | .20 (5.08) | .03 (14) |
| EC100F-3 | 3 | .30 (7.6) | .04 (18) |
| EC100F-4 | 4 | .40 (10.2) | .06 (27) |
| EC100F-5 | 5 | .50 (12.7) | .07 (32) |
| EC100F-6 | 6 | .60 (15.2) | .09 (41) |
| EC100F-7 | 7 | .70 (17.8) | .10 (45) |
| EC100F-8 | 8 | .80 (20.3) | .12 (54) |
| EC100F-9 | 9 | .90 (22.9) | .13 (59) |
| EC100F-10 | 10 | 1.00 (25.4) | .15 (68) |
| EC100F-11 | 11 | 1.10 (27.9) | .16 (73) |
| EC100F-12 | 12 | 1.20 (30.5) | .17 (77) |
| EC100F-13 | 13 | 1.30 (33.0) | .19 (86) |
| EC100F-14 | 14 | 1.40 (35.6) | .20 (91) |
| EC100F-15 | 15 | 1.50 (38.1) | .22 (100) |
| EC100F-16 | 16 | 1.60 (40.6) | .23 (104) |
| EC100F-17 | 17 | 1.70 (43.2) | .25 (113) |
| EC100F-18 | 18 | 1.80 (45.7) | .26 (118) |
| EC100F-19 | 19 | 1.90 (48.3) | .28 (127) |
| EC100F-20 | 20 | 2.00 (50.8) | .29 (132) |
| EC100F-21 | 21 | 2.10 (53.3) | .31 (141) |
| EC100F-22 | 22 | 2.20 (55.9) | .32 (145) |
| EC100F-23 | 23 | 2.30 (58.4) | .33 (150) |
| EC100F-24 | 24 | 2.40 (61.0) | .35 (159) |
| EC100F-25 | 25 | 2.50 (63.5) | .36 (163) |
| EC100F-26 | 26 | 2.60 (66.0) | .38 (172) |
| EC100F-27 | 27 | 2.70 (68.6) | .39 (177) |
| EC100F-28 | 28 | 2.80 (71.1) | .41 (186) |

U.L. RECOGNIZED FILE # E73711

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER PACKAGE SIZE SUFFIX.
- COVER MATERIAL: THERMOPLASTIC U.L. 94V-0.
- ALL DIMENSIONS ARE SHOWN IN INCHES AND [MILLIMETERS].
- TWO DEPRESSIONS ON COVER FOR FIVE (5) OR MORE CIRCUITS.
- PARTS ARE SOLD AS "FUNCTIONAL ONLY".



| REV | DATE | BY | CHK | DESCRIPTION | CN - R | CUST | SUP |
|-----|-----------|-----|-----|---|--------|------|-----|
| 13 | 7/26 /11 | KLR | | REMOVED DIMENSIONS | | | |
| 12 | 5/26 /11 | KLR | | EC100F-2 DIMENSION "A" WAS .22 | | | |
| 11 | 9/27 /05 | KLR | | ADDED RoHS SYMBOL | 2162 | | |
| 10 | 02/13 /02 | JAT | | ADDED PDF FILE AND REVISED MFG LOCATION | 2025 | | |
| 9 | | JEP | | RELEASED | 1865 | | |

www.pancon.de / GERMANY
www.panconconnectors.com / USA

Bolingbrook, Illinois

MAS-CON®, .100" END CIRCUIT SOCKET COVER

| | |
|--|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ±.02 (A) ANGLES ± 3° | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION. SCALE 2 : 1 |
|--|---|

| | |
|------------------|------------|
| DRAWN BY RIC | MAT'L |
| DATE 10/28/85 | SEE NOTE 2 |
| CHK'D SCR | |

| | |
|-------------------------|--------------------------|
| DRAWING NO. KA-10068 | DWG. A SIZE |
|-------------------------|--------------------------|