




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		T		REVISED PER ECO-14-001013	22Jan2014	H.M	M.L



- NOTES:
- 100% ELECTRICAL TEST.
 - PACKAGE: 1PCS/PE BAG.
 - PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.

PART NO.	LENGTH(L)	CABLE AWG	CABLE O.D. (REF)
1496476-1	1000 ⁺⁰ ₋₃₀ MM	1P*28AWG+2C*26AWG	4.2 mm
1496476-2	1500 ⁺⁰ ₋₃₀ MM	1P*28AWG+2C*24AWG	4.5 mm
1496476-3	2000 ⁺⁰ ₋₃₀ MM	1P*28AWG+2C*24AWG	4.5 mm
1496476-4	3000 ⁺⁰ ₋₅₀ MM	1P*25AWG+2C*22AWG	5.2 mm
1496476-5	5000 ⁺⁰ ₋₅₀ MM	1P*25AWG+2C*20AWG	5.2 mm
1496476-6	305 ⁺⁰ ₋₃₀ MM	1P*28AWG+2C*28AWG	3.5 mm



-	-	-	-	AR	AR	MR	UL TAPE, W: 9MM, COLOR: BLACK	12
1	-	-	-	-	-	PC	CONNECTOR,MINI USB B TYPE	11
-	-	-	1	1	1	PC	CONNECTOR,MINI USB B TYPE	10
AR	AR	AR	AR	AR	AR	MR	Heat Shrink Tubing 1.0MM BLACK	9
AR	AR	AR	AR	AR	AR	MR	Copper Foil, W: 5.0MM	8
-	AR	AR	-	-	-	MR	Heat Shrink Tubing, 1.5mm, Color: Black	7
-	-	-	-	-	AR	MR	PVC TUBE, ID: 1.5MM, COLOR: BLACK	7
AR	-	-	AR	AR	-	MR	Heat Shrink Tubing, 1.0mm, Color: Black	7
1	1	1	1	1	1	PC	LABEL , 25*35mm.	6
AR	AR	AR	AR	AR	AR	MR	Copper Foil, W: 10.0MM.	5
AR	AR	AR	AR	AR	AR	MR	USB 2.0 Cable, 1P(Signal)+2C(Power)+Al/Mylar +Drain+Braid, Color: Black.	4
-	1	1	-	-	-	PC	Mini USB, B PLUG, SOLDER TYPE	3
AR	AR	AR	AR	AR	AR	KG	Overmolded PVC,Color: Black(BK01).Shore A 80±5	2
1	1	1	1	1	1	PC	USB A Type Solder Contacts: Gold Plated 30U" Shell: Nickel Plated, Insulation: White	1
-6	-5	-4	-3	-2	-1	U/M		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	BOVEY LIU	28/JUN/01
CHK	BEVIN	28/JUN/01
APVD	MARK	28/JUN/01

TE Connectivity

NAME: CABLE ASSY, MINI USB B TYPE TO USB A TYPE

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 1496476

SCALE: N.T.S. SHEET: 1 OF 1 REV: T