






NOTES:

1. MATERIAL: SEE CHART
2. FINISH: SEE CHART
3. PRODUCT SPECIFICATION PS-10-07
4. 芯ズレ 0.13最大
DIM 1.98±0.25 TO BE SYMMETRICAL
WITHIN 0.13 T.I.R
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF
COSMETIC SPECIFICATION PS-45499-002

0.55 WAS 0.34 EC NO: UCP2015-0313 DRAWN: KIPPER 2014/07/23 CHKD: J.BELL 2014/07/23 APPR: FSMITH 2014/07/31	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
						DRAWN BY DATE		TITLE		
			4 PLACES ± --- ± ---			K. KOHAMA 2000/03/28		MINI.KK.CRIMP TYPE TERM		
			3 PLACES ± --- ± ---			CHECKED BY DATE				
			2 PLACES ± --- ± ---			K. ASAKAWA 2002/04/08				
			1 PLACE ± --- ± ---			APPROVED BY DATE				
			0 PLACE ± ±							
			ANGULAR ± ---°			MATERIAL NO.		DOCUMENT NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-2759*		
						SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 1		

39-00-0107	2759PBT	バラ状 LOOSE	0.00091 MIN REFLOWED TIN	リン 青銅 PHOS BRO.
39-00-0064	PBT	連鎖状 CHAIN		
39-00-0381	PBGL	バラ状 LOOSE	SELECTIVE GOLD: 0.00038 MIN. OVERALL GOLD FLASH: 0.00005-0.00025 OVERALL NICKEL UNDERPLATE: 0.00076 MIN.	
39-00-0380	PBG	連鎖状 CHAIN		
39-00-0377	GL	バラ状 LOOSE	SELECTIVE GOLD: 0.00038 MIN. OVERALL GOLD FLASH: 0.00005-0.00025 OVERALL NICKEL UNDERPLATE: 0.00076 MIN.	黄銅 BRASS
39-00-0376	G	連鎖状 CHAIN		
39-00-0374	GS	連鎖状 CHAIN		
39-00-0373	TL	バラ状 LOOSE	0.00089 MIN REFLOWED TIN OVER 0.00051 MIN COPPER UNDERPLATE	材質 MATL
39-00-0372	2759 T	連鎖状 CHAIN		
EDP.NO.	ENG.NO.	端子形状 FORM	メッキ仕様 FINISH	

DWG. NO. SD-2759*

F

D

C

B

DO NOT SCALE DRAWING

8 7 6 5 4 3 2 1

F

E







D

C

B

A

S2759.S01



注)
NOTE.
1. 芯ズレ 0.13最大
DIM 1.98⁺⁰_{-0.25} TO BE SYMMETRICAL
WITHIN 0.13 T.I.R

39-00-0381	2759PBGL	バラ状 LOOSE	NI:2.0UMIN. AU:0.35UMIN.	リン 青銅 PHOS BRO.
39-00-0380	PBG	連鎖状 CHAIN		
39-00-0379	G5L	バラ状 LOOSE	NI:2.0UMIN. AU:0.5UMIN.	黄銅 BRASS
39-00-0378	G5	連鎖状 CHAIN		
39-00-0377	GL	バラ状 LOOSE	NI:2.0UMIN. AU:0.35UMIN.	
39-00-0376	2759G	連鎖状 CHAIN		
EDP.NO.	ENG.NO.	端子形状 FORM	メッキ仕様 FINISH	材質 MATL

T04NO. DRAWN: CHK: APPR:		T03NO. DRAWN: CHK: APPR:		REVISED T02NO. J2004-3591 DRAWN: A.IDA CHK: H.TAKASE APPR: YO.ITO		REVISED T01NO. J2002-2529 DRAWN: T.ASAKAWA CHK: K.ASAKAWA APPR: T.YAMAGUCHI		REDRAWN T00NO. JC2000-0628 DRAWN: K.KOHAMA CHK: T.YAMAGUCHI APPR: M.FUKUSHIMA		DESCRIPTION		MATERIAL 材料 表参照 板厚: 0.203 SEE TABLE 0.203 THK		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE 10:1		DESIGN UNITS mm INCH		THIRD ANGLE PROJECTION		SHEET NO. 1		REV ON CAD ONLY	
				W		V		U		REV		FINISH 仕上げ 表参照 SEE TABLE		10 UNDER 未満 ±0.2		DRAWN BY & DATE K.KOHAMA '00/ 3/28		CHECKED BY & DATE K.ASAKAWA '02/04/08		APPROVED BY & DATE T.YAMAGUCHI '02/04/08		TITLE: MINI. KK. CRIMP TYPE TERM.			
												WIRE RANGE 適用線径範囲 AWG#22-#28		30 OVER 以上 ±0.3		ANGLE 角度 ±3°		CAD FILENAME S2759.S01		MATERIAL NO. 2759*		DRAWING NO. SD-2759*		SHEET NO. 1	
												INS. RANGE 被覆外径 φ(1.2)-φ1.7										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE B	

8 7 6 5 4 3 2 1 EN-02J(097) MXJ-54