


DADT	NI	\sim

SH-302

	REVISIONS							
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	А	RELEASED	Jagan	06/04/09	Suresh	06/04/09	Farnell	24/04/09

Shapes and Dimensions/Circuit Diagram



Dimensions: Millimetres

Part Number Table

Rated Voltage (V dc)	Rated Current (A)	Minimum Inductance (μΗ)	Maximum DC Resistance (MΩ/line)	Operating Temperature Range (°C)	Part Number	
150	3.0	7.5	26	-25 to +80	SH-302	

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group by liability for death or personal injury resulting from its negligence.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

TOLERANCES:

DRAWN BY:	DATE:
Shalini	06/04/09
CHECKED BY:	DATE:
Suresh	06/04/09
APPROVED BY:	DATE:
Farnell	24/04/09

DRAWING TITLE:			Choke - Common	Mod	e, 2 x 7.5Uh	
_	SIZE A	DWG NO.	M10002048	l .	TRONIC FILE 8_DWG	REV A
SCALE: NTS		E: NTS	U.O.M.: mm		SHEET: 1 OI	- 1