






- NOTES**
- 1 - UNIT INCLUDES CATALOG LISTING "ISM" TYPE BASIC SWITCH (2)
 - 2 SPRING LATCH PERMITS ASSEMBLY AND DISASSEMBLY AS REQUIRED
 - 3 "D" SHAPED HOLE IN SPRING LATCH PREVENTS ROTATION BETWEEN THE TWO PARTS
 - 4 - ASSEMBLY IS COMPLETED AFTER INSTALLING BUTTON TO PANEL
 - 5 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
 - 6 - TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — 3 LB APPROX
PLUNGER TRAVEL — — — .060 APPROX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (2)

250 VAC — — — — — 5 AMP
30 VOLTS DC RATING
INDUCTIVE — — — — — SEA LEVEL — — — 3 AMP
50,000 FT — — — 2.5 AMP
RESISTIVE — — — — — SEA LEVEL — — — 5 AMP
50,000 FT — — — 5 AMP
MAXIMUM INRUSH — — — — — 24 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT

2 P B 4

PAGE 1 OF 1

M

DRAWING
NUMBER

8

ISSUE

REPLACES

RELEASE NO.

CHECK

CHECK

APR 65

LS D

CHECK

31 MAR 65

MB F

DRAWN

31 MAR 65

FORMTEK

FO-50378