



ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT						BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT						CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION				BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	CPA	MAT SEAL	RING SEAL						
MX150 ASSY RCP 2X2 CS BK A/4	334720501	A-BLACK-CLIP	GCO	PLR		M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS LG B/4	334720502	B-LIGHT GRAY-CLIP	GCO	PLR		M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS DG C/4	334720503	C-DARK GRAY-CLIP	GCO	PLR		M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS SG D/4	334720504	D-STONE GRAY-CLIP	GCO	PLR		M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS YW A/4	334720505	A-YELLOW-CLIP	GCO	PLR		M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS CPA BK A/4	334720506	A-BLACK-CLIP	GCO	PLR	CPA	M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS CPA LG B/4	334720507	B-LIGHT GRAY-CLIP	GCO	PLR	CPA	M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS CPA DG C/4	334720508	C-DARK GRAY-CLIP	GCO	PLR	CPA	M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS CPA SG D/4	334720509	D-STONE GRAY-CLIP	GCO	PLR	CPA	M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 CS CPA YW A/4	334720510	A-YELLOW-CLIP	GCO	PLR	CPA	M	R	-	-	DESIGN RELEASE		N/A	N/A
MX150 ASSY RCP 2X2 BK A/4	334724001	A-BLACK	GCO	PLR		M	R	-	-	SALEABLE		N/A	N/A
MX150 ASSY RCP 2X2 LG B/4	334724002	B-LIGHT GRAY	GCO	PLR		M	R	-	-	SALEABLE		N/A	N/A
MX150 ASSY RCP 2X2 BR C/4	334724003	C-BROWN	GCO	PLR		M	R	-	-	NOT RECOMMENDED	SEE 334724042	N/A	N/A
MX150 ASSY RCP 2X2 GR D/4	334724004	D-GREEN	GCO	PLR		M	R	-	-	NOT RECOMMENDED	SEE 334724043	N/A	N/A
MX150 ASSY RCP 2X2 CPA BK A/4	334724006	A-BLACK	GCO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A



MX150 RECEPTACLE 2X2 SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT						BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT						CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION				BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	CPA	MAT SEAL	RING SEAL						
MX150 ASSY RCP 2X2 CPA LG B/4	334724007	B-LIGHT GRAY	GCO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA BR C/4	334724008	C-BROWN	GCO	PLR	CPA	M	R	-	-	NOT RECOMMENDED	SEE 334724044	N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA GR D/4	334724009	D-GREEN	GCO	PLR	CPA	M	R	-	-	NOT RECOMMENDED	SEE 334724045	N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 BK A/0	334724031	A-BLACK	GCP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 LG B/0	334724032	B-LIGHT GRAY	GCP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 BR C/0	334724033	C-BROWN	GCP	PLR		M	R	1	2	NOT RECOMMENDED	SEE 334724046	N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 GR D/0	334724034	D-GREEN	GCP	PLR		M	R	1	2	NOT RECOMMENDED	SEE 334724047	N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 BK A/2	334724035	A-BLACK	GCP	PLR		M	R	-	2	SALEABLE		N/A	N/A
								3	-				
MX150 ASSY RCP 2X2 BK A/1	334724036	A-BLACK	GCP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	-				
MX150 ASSY RCP 2X2 BK A/2	334724037	A-BLACK	GCP	PLR		M	R	-	-	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 BK A/3	334724038	A-BLACK	GCP	PLR		M	R	-	-	SALEABLE		N/A	N/A
								3	-				
MX150 ASSY RCP 2X2 BK A/3	334724039	A-BLACK	GCP	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	4				
MX150 ASSY RCP 2X2 BK A/3	334724040	A-BLACK	GCP	PLR		M	R	-	2	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 BK A/2	334724041	A-BLACK	GCP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 DG C/4	334724042	C-DARK GRAY	GCO	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 SG D/4	334724043	D-STONE GRAY	GCO	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA DG C/4	334724044	C-DARK GRAY	GCO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA SG D/4	334724045	D-STONE GRAY	GCO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 DG C/0	334724046	C-DARK GRAY	GCP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 SG D/0	334724047	D-STONE GRAY	GCP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 BK A/2	334724048	A-BLACK	GCP	PLR		M	R	-	2	SALEABLE		N/A	N/A
								-	4				
MX150 ASSY RCP 2X2 CPA BK A/3	334724049	A-BLACK	GCP	PLR	CPA	M	R	-	2	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA BK A/3	334724050	A-BLACK	GCP	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								3	-				
MX150 ASSY RCP 2X2 CPA BK A/3	334724051	A-BLACK	GCP	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	4				
MX150 ASSY RCP 2X2 BK A/2	334724052	A-BLACK	GCP	PLR		M	R	-	2	SALEABLE		N/A	N/A
								-	4				
MX150 ASSY RCP 2X2 CPA YW A/4	334724053	A-YELLOW	GCO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 BK A/2	334724054	A-BLACK	GCP	PLR		M	R	1	-	SALEABLE		N/A	N/A
								3	-				




MX150 RECEPTACLE 2X2 SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET


ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT						BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT						CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION				BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	CPA	MAT SEAL	RING SEAL						
MX150 ASSY RCP 2X2 CPA LG B/3	334724055	B-LIGHT GRAY	GCP	PLR	CPA	M	R	1	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 BK A/3	334724056	A-BLACK	GCP	PLR		M	R	1	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA BK A/0	334724057	A-BLACK	GCP	PLR	CPA	M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 CPA BK A/2	334724058	A-BLACK	GCP	PLR	CPA	M	R	-	2	SALEABLE		N/A	N/A
								3	-				
MX150 ASSY RCP 2X2 BK A/2	334724059	A-BLACK	GCP	PLR		M	R	1	-	SALEABLE		N/A	N/A
								-	4				
MX150 ASSY RCP 2X2 LG B/2	334724060	B-LIGHT GRAY	GCP	PLR		M	R	-	2	SALEABLE		N/A	N/A
								-	4				
MX150 ASSY RCP 2X2 XC BK A/4	334724101	A-BLACK	GCLO	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC LG B/4	334724102	B-LIGHT GRAY	GCLO	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC DG C/4	334724103	C-DARK GRAY	GCLO	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC SG D/4	334724104	D-STONE GRAY	GCLO	PLR		M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC CPA BK A/4	334724105	A-BLACK	GCLO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC CPA LG B/4	334724106	B-LIGHT GRAY	GCLO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC CPA DG C/4	334724107	C-DARK GRAY	GCLO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC CPA SG D/4	334724108	D-STONE GRAY	GCLO	PLR	CPA	M	R	-	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC BK A/0	334724109	A-BLACK	GCLP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 XC LG B/0	334724110	B-LIGHT GRAY	GCLP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 XC DG C/0	334724111	C-DARK GRAY	GCLP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 XC SG D/0	334724112	D-STONE GRAY	GCLP	PLR		M	R	1	2	SALEABLE		N/A	N/A
								3	4				
MX150 ASSY RCP 2X2 CPA SG D/3	334724113	D-STONE GRAY	GCP	PLR	CPA	M	R	1	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA DG C/3	334724114	C-DARK GRAY	GCP	PLR	CPA	M	R	1	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 CPA BK A/3	334724115	A-BLACK	GCP	PLR	CPA	M	R	1	-	SALEABLE		N/A	N/A
								-	-				
MX150 ASSY RCP 2X2 XC CPA SG D/3	334724116	D-STONE GRAY	GCLP	PLR	CPA	M	R	1	-	SALEABLE		N/A	N/A
								-	-				

SHEET DESCRIPTION


CONFIGURATIONS




2X2 - STD.
2X2 - TRNS. - SILICONE FREE †




2X2 - STD. - WITH CLIPSLOT *




† 2X2 - UL V0




2X2 - STD. - LENGTHENED




2X3 - STD.
2X3 - TRNS. - CONTAINS SILICONE †




2X3 - STD. - WITH CLIPSLOT *




2X4 - STD.




2X4 - STD. - WITH CLIPSLOT *




† 2X4 - UL V0




† 2X4 - UL V0-WITH CLIPSLOT*




2X6 - STD.
C1 † 2X6 - TRNS.




2X6 - STD. - WITH CLIPSLOT *
C1 † 2X6 - TRNS. - WITH CLIPSLOT *




† 2X6 - UL V0




2X8 - STD.




2X8 - STD. - WITH CLIPSLOT *



2X10 - STD.



2X10 - STD. - WITH CLIPSLOT *



† 2X10 - UL V0


* WITH CLIPSLOT CONFIGURATION DOES NOT
MEET THE USCAR PACKAGING FRAME REQUIREMENTS
† MINOR GEOMETRY DIFFERENCE THAN STANDARD CONFIGURATION
SEE NOTES 1a & 2a-b FOR MORE INFORMATION

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC:								
	mm		1:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27										
	ANGULAR TOL ± 1.0 °												
	4 PLACES ±												
	3 PLACES ±												
	2 PLACES ± 0.1												
	1 PLACE ± 0.2		PRODUCT CUSTOMER DRAWING										
	0 PLACES ±												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
		A1-SIZE		33472		SD-33472-0001		PSD		001		C2	
						MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
								GENERAL MARKET				2 OF 11	


SHEET DESCRIPTION

KEY CONFIGURATIONS


2X2




KEY A



KEY B




KEY C




KEY D


2X3




KEY A



KEY B




KEY C




KEY D


2X4




KEY A



KEY B



KEY C




KEY D

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
▮ = 0		DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex					
▮ = 0		mm		1:1													
▮ = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650						MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL					
▮ = 0		ANGULAR TOL ± 1.0 °															
▮ = 0		4 PLACES		±		DRWN: DDEB 2018/01/19						PRODUCT CUSTOMER DRAWING					
▮ = 0		3 PLACES		±		CHK'D: MVANSLAMBROU 2018/02/16											
▮ = 0		2 PLACES		± 0.1		APPR: MVANSLAMBROU 2018/02/16											
▮ = 0		1 PLACE		± 0.2		INITIAL REVISION:						DOCUMENT NUMBER SD-33472-0001					
▮ = 0		0 PLACES		±		DRWN: APROFFITT 2014/05/14										DOC TYPE PSD	
▮ = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING A1-SIZE		SERIES 33472		MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 3 OF 11	
▮ = 0						▮ = 0											


SHEET DESCRIPTION

KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



KEY B




KEY C




KEY D


2X10




KEY A



KEY B



KEY C



KEY D



SYMBOLS = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	1:1
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL ± 1.0 °	
	= 0	4 PLACES ±
	= 0	3 PLACES ±
	= 0	2 PLACES ± 0.1
	= 0	1 PLACE ± 0.2
	= 0	0 PLACES ±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		
THIRD ANGLE PROJECTION		
DRAWING SERIES		
A1-SIZE 33472		

CURRENT REV DESC:		
EC NO: 171650		
DRWN: DDEB	2018/01/19	
CHK'D: MVANSLAMBROU	2018/02/16	
APPR: MVANSLAMBROU	2018/02/16	
INITIAL REVISION:		
DRWN: APROFFITT	2014/05/14	
APPR: VKOSHY	2014/06/27	

molex		
MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL		
PRODUCT CUSTOMER DRAWING		
DOCUMENT NUMBER	DOC TYPE	DOC PART
SD-33472-0001	PSD	001
MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	GENERAL MARKET	4 OF 11









SHEET DESCRIPTION

RECEPTACLE CONNECTOR ASSEMBLY




B APPLIES TO 2X2 - STD. - WITH CLIPSLOT ONLY

DESCRIPTION	DIMENSIONS						
	A	B	C	D	E	F	J
2X2 W/O CLIPSLOT	18.58	1.75	25.45	24.81	37.65	N/A	2.75±0.50
2X2 W/ CLIPSLOT	18.58	1.75	27.65	24.81	37.65	N/A	2.75±0.50
2X2 LENGTHENED	18.58	1.75	25.45	24.81	42.25	N/A	2.75±0.50
2X3 W/ CLIPSLOT	22.25	3.5	30.50	N/A	37.65	27.96	4.0±0.4
2X3 W/O CLIPSLOT	22.25	3.5	26.24	24.90	37.65	N/A	4.0±0.4
2X4 W/ CLIPSLOT	25.75	1.75	31.50	N/A	37.65	28.00	2.75±0.50
2X4 W/O CLIPSLOT	25.75	1.75	29.19	24.81	37.65	N/A	2.75±0.50
2X6 W/ CLIPSLOT	32.75	1.75	35.58	N/A	37.65	27.76	2.75±0.50
2X6 W/O CLIPSLOT	32.75	1.75	35.58	24.90	37.65	N/A	2.75±0.50
2X6 W/O CLIPSLOT V0	32.75	1.75	35.58	25.0	37.65	N/A	2.75±0.50
2X8 W/O CLIPSLOT	39.80	1.75	42.25	24.90	37.65	N/A	4.0±0.4
2X8 W/ CLIPSLOT	39.80	1.75	42.25	N/A	37.65	27.80	4.0±0.4
2X10 W/O CLIPSLOT	46.75	1.75	49.95	24.90	37.65	N/A	2.75±0.50
2X10 W/ CLIPSLOT	46.75	1.75	49.95	N/A	37.65	27.80	2.75±0.50



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION

SECTION Y-Y



SECTION Z-Z

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex									
	mm		1:1																
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL									
	ANGULAR TOL ± 1.0 °																		
	4 PLACES		±		INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27					PRODUCT CUSTOMER DRAWING									
	3 PLACES		±																
	2 PLACES		± 0.1		DOCUMENT NUMBER SD-33472-0001					DOC TYPE PSD		DOC PART 001		REVISION C2					
	1 PLACE		± 0.2																
	0 PLACES		±		THIRD ANGLE PROJECTION					DRAWING A1-SIZE		SERIES 33472		MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 5 OF 11	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																		

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:25
-----------------	----	--------------	------------	----------

BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:

- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH RECEPTACLE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33472-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34951-0001.

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34951-XXXX

CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR


MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20


RECEPTACLE SEALED ASSEMBLY

BACKSHELL (BKS)






SCALE 2:1

90° ADAPTOR




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex				
	mm		1.5:1											
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL				
 = 0														
 = 0	ANGULAR TOL ± 1.0 °				PRODUCT CUSTOMER DRAWING					DOCUMENT NUMBER SD-33472-0001 DOC TYPE PSD DOC PART 001 REVISION C2				
 = 0	4 PLACES ±													
 = 0	3 PLACES ±				INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27					MATERIAL NUMBER DRAWING A1-SIZE SERIES 33472				
 = 0	2 PLACES ± 0.1													
 = 0	1 PLACE ± 0.2				THIRD ANGLE PROJECTION 					CUSTOMER GENERAL MARKET				
 = 0	0 PLACES ±													
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SHEET NUMBER 6 OF 11									
= 0														

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	



V

V





Partial V-V
SCALE 4:1

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC:												
	mm		4:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27												
	ANGULAR TOL ± 1.0 °																
	4 PLACES		±														
	3 PLACES		±														
	2 PLACES		± 0.1														
	1 PLACE		± 0.2						PRODUCT CUSTOMER DRAWING								
	0 PLACES		±														
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION
						A1-SIZE		33472		SD-33472-0001		PSD		001		C2	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
												GENERAL MARKET				7 OF 11	



DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:25
-----------------	----	--------------	---------------------

SHEET DESCRIPTION

MOLEX BACKSHELL CONFIGURATIONS



RECEPTACLE SEALED ASSEMBLY WITH RECEPTACLE BACKSHELL












ADD THE VALUE OF 'L' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED

CHARTED DIMENSIONS				
DESCRIPTION	DIMENSIONS			
	J	K	L	M
2X2 W/O CLIPSLOT	TBD	TBD	TBD	TBD
2X2 W/ CLIP SLOT	TBD	TBD	TBD	TBD
2X2 LENGTHENED	TBD	TBD	TBD	TBD
2X4 W/ CLIPSLOT	58.39	32.85	32.10	44.26
2X4 W/O CLIPSLOT	N/A	N/A	N/A	N/A
2X8 W/ CLIPSLOT	67.19	42.65	36.10	56.49
2X8 W/O CLIPSLOT	N/A	N/A	N/A	N/A
2X10 W/ CLIPSLOT	67.19	42.65	36.10	56.49
2X10 W/O CLIPSLOT	N/A	N/A	N/A	N/A


SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
		DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex							
= 0		mm		2.5:1		EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27						MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL							
= 0		GENERAL TOLERANCES (UNLESS SPECIFIED)																	
= 0		ANGULAR TOL ± 1.0 °										PRODUCT CUSTOMER DRAWING							
= 0		4 PLACES ±										DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
= 0		3 PLACES ±										SD-33472-0001		PSD		001		C2	
= 0		2 PLACES ± 0.1				THIRD ANGLE PROJECTION		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER							
= 0		1 PLACE ± 0.2						A1-SIZE		33472		GENERAL MARKET		10 OF 11					
= 0		0 PLACES ±																	
= 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:25
-----------------	----	--------------	---------------------





150-S-020-2-D02	D	STONE GRAY
150-S-020-2-C02	C	DK GRAY
150-S-020-2-B02	B	LT GRAY
150-S-020-2-A02	A	BLACK
P/N	OPTION	MATING CONNECTOR COLOR


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:25
-----------------	----	--------------	------------	----------



CONSTRUCTION BELOW THIS SURFACE IS NOT CONTROLLED BY EWCAP. NO PLASTIC FEATURES MAY EXTEND ABOVE THIS SURFACE.



SURFACE MUST BE FREE OF SURFACE DEFECTS AND PARTING LINES FOR SEALING ALL AROUND



SECTION B-B

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
	0.05 mm
	0.10 mm
	0.20 mm
	0.30 mm
	0.50 mm
	0.75 mm
	1.00 mm
	1.50 mm
	2.00 mm
	2.50 mm
	3.00 mm
	4.00 mm
	5.00 mm
	6.00 mm
	8.00 mm
	10.00 mm
	12.00 mm
	15.00 mm
	20.00 mm
	25.00 mm
	30.00 mm
	40.00 mm
	50.00 mm
	60.00 mm
	80.00 mm
	100.00 mm

- MATING INTERFACE NOTES: VALID UNLESS OTHERWISE SPECIFIED
- GENERAL:
 - DESIGNED TO MATE WITH MOLEX CONNECTOR 33472-2XXX & 160008-0XXX & 160074-0XXX
 - A FULL SHROUD ON THE MATING CONNECTOR IS REQUIRED TO INSURE THAT THE CONNECTOR-HEADER POLARIZATION FEATURES (OPTIONS A THRU D) WILL FUNCTION. THE FULL SHROUD ALSO PREVENTS SCOOP DAMAGE TO THE HEADER PINS. REFER TO 'SAE/USCAR-12 CONNECTOR DESIGN GUIDE LINES' FOR ADDITIONAL INFORMATION
 - PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: ES-40000-5016
 - FLAMMABILITY REQUIREMENT: PER ISO3795 OR GM3191
 - BURN RATE 100mm/MIN MAXIMUM
 - MATERIAL MUST BE SELF EXTINGUISHING
 - MATERIALS:
 - MATERIAL: SPS/NYLON GF20, REGRIND 20% MAX BY WEIGHT
 - STANDARD COLORS FOR POLARIZATION (SEE KEYING OPTIONS TABLE). DEVIATION REQUIRES APPROVAL OF AUTHORIZED PERSON
 - FOR BLADE BASE MATERIAL, PLATING AND PROCESS LUBRICANT:
 - TIN: - BASE MATERIAL: COPPER ALLOY, CONDUCTIVITY >=60% IACS AT 20°C; TENSILE STRENGTH >= 410 N/mm² - BARRIER MATERIAL: NICKEL DEPOSIT FROM NICKEL SULFAMATE PLATING SOLUTION W/O ANY ADDITIVES THICKNESS: 1.25 - 2.25 MICROMETERS - TOP LAYER: 100% ELECTRO-DEPOSITED TIN, MATTE FINISH THICKNESS: 2.5 - 4.0 MICROMETERS
 - SILVER: - BARRIER MATERIAL: ELECTRO-DEPOSITED DUCTILE SULPHAMATE NICKEL THICKNESS: 1.25 - 2.25 MICROMETERS - TOP LAYER: ELECTRO-DEPOSITED SEMI-BRIGHT PURE SILVER (0.5% MAX IMPURITIES) OVER NICKEL ANTI-TARNISH TREATMENT EVERBRIGHT WS THICKNESS: 1.9 - 3.3 MICROMETERS
 - BLADES MUST CONFORM TO ES-40000-5007, EXCEPT FOR SPECULAR REFLECTIVITY - SECTION 6.0
 - ANY PROCESS LUBRICANT REMAINING ON THE TERMINAL MUST NOT VARNISH OR DEGRADE IT'S ELECTRICAL PERFORMANCE UP TO A MAXIMUM CLASS AMBIENT TEMPERATURE PER SAE USCAR-2 FOR 1008 HOURS, PROCESS LUBRICANTS SHOULD BE APPROVED BY THE RESPONSIBLE ENGINEER
 - INFORMATION FOR BLADE DESIGN WAS DEVELOPED FROM EWCAP DWG: EWCAP-001
 - GEOMETRY:
 - THIS IS A 100% CAD GENERATED PART. THE CAD MATHEMATICAL DATA IS THE MASTER FOR THIS PART. FOR DIMENSIONAL OR ANY INFORMATION NOT SHOWN ON THIS DRAWING, ANALYZE THE CAD MODEL.
 - GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994
 - GENERAL TOLERANCES: SEE TITLE BLOCK
 - EDGES AND UNDIMENSIONED DETAILS PER ISO13715
 - MANUFACTURING:
 - DRAFT TO BE WITHIN TOLERANCE. PLUS DRAFT - INDICATES A DIMENSION REPRESENTS THE SMALLEST SIZE OF A FEATURE. DRAFT WILL ADD MATERIAL. MINUS DRAFT - INDICATES A DIMENSION REPRESENTS THE LARGEST SIZE OF A FEATURE. DRAFT WILL REMOVE MATERIAL.
 - ALLOWABLE FLASH MAX 0.20 HIGH BY MAX 0.13 THICK.
 - ALLOWABLE SPLIT/PARTING LINE MISMATCH 0.2 MAX.
 - VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B)
 - NO EXTERNAL MOLD RELEASE AGENT ALLOWED DURING MANUFACTURING
 - NO PARTING LINES, NO DRAFT, MISMATCHES OR EJECTOR MARKS PERMISSIBLE WITHIN SEALING SURFACE. SEALING SURFACE TOOLING TO BE PROCESSED

CURRENT REV DESC:		molex	
EC NO: 171650		MX150 RCPT	
DRWN: DDEB		DUAL ROW SEALED ASSEMBLY MAT SEAL	
CHK'D: MVANSLAMBROU		PRODUCT CUSTOMER DRAWING	
APPR: MVANSLAMBROU		DOCUMENT NUMBER	
INITIAL REVISION:		SD-33472-0001	
DRWN: APROFFITT		DOC TYPE	
APPR: VKOSHY		DOC PART	
THIRD ANGLE PROJECTION		DOC REVISION	
DRAWING		PSD	
SERIES		001	
MATERIAL NUMBER		C2	
CUSTOMER		GENERAL MARKET	
SHEET NUMBER		11 OF 11	