


ISS.	AMEND	DATE
1	ISSUED	12/02/2015
2	REAR USB ROTATE 90°	30/09/2015



HOLES TO SUIT
SCREW USED

PANEL CUTOUT
MAXIMUM PANEL
THICKNESS 3MM





Material:

1. Insert: ABS
2. Frame: Polyamide
3. Shell: Nickel plated steel
4. Contacts: Gold Plated



Notes:

1. Voltage rating: 30V ac
2. Current rating: 1.8 A max
3. Contact resistance: 50mΩ max
4. Insulation resistance: 20MΩ min
5. Dielectric withstanding voltage: 500V AC
6. Operating Temperature: -20°C to 50°C

VARIANTS	
PART NO.	HOLE DETAILS
CP30206N	HOLE $\varnothing 3.50$ X CSK 82° X $\varnothing 5.85$
CP30206NX	PLAIN HOLE $\varnothing 2.50$



2 HOLES: $\varnothing 3.5$ MM
CSK 82° X $\varnothing 5.85$
'X' VERSION HAS $\varnothing 2.5$
HOLES.



RoHS
COMPLIANT

TOLERANCE
NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE \varnothing ±
ANGLES ±
UNLESS
OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2015

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

DO NOT SCALE

MATERIAL: See Notes

FINISH: See Notes

DRAWN: D.P.J.

APPROVED: D.P.J.

TITLE: FEED THROUGH USB 3.0 B to USB 3.0 A, Nickel Plated

DRWG. No. **CP30206N**

FORM: A4DRWGH