




3xM4 ∇ 8mm
(x120°)

3xM3 ∇ 6mm
(x120°)

9,5 Flat

Ø 48



UNCONTROLLED COPY

FIRST ISSUE DATE : 21/10/2021
DRAWN : RHM
APPROVED : JHH
DATE : 21/10/2021

SENSATA TECHNOLOGIES PROPRIETARY AND
CONFIDENTIAL. NEITHER THIS PRINT NOR THE
INFORMATION CONTAINED HEREON IS TO BE USED
AGAINST THE INTERESTS OF SENSATA TECHNOLOGIES
OR AGAINST THE INTERESTS OF ANY OF ITS AFFILIATED
COMPANIES OR WHOLLY OWNED SUBSIDIARIES.

ECN :


DATE : 21/10/2021

Housing material : Steel
Flange material : Aluminum
Shaft material : Stainless Steel

UNLESS OTHERWISE
SPECIFIED DIMENSIONS ARE IN MILLIMETERS
[INCHES] AND ARE INTENDED
AS NOMINAL. SEE PRODUCT SPECIFICATION
FOR MORE DETAILS.

DO NOT
SCALE
DRAWING

EUROPEAN
SYSTEM



BEI SENSORS SAS
Espace Européen de l'Entreprise
9, rue de Copenhague
BP 70044 - F 67013 STRASBOURG Cedex
Tel : +33 (0)3 88 20 81 40

BEI Sensors

TITLE
THM510_M12 connector
Output_Radial

SIZE
A3

DWG NO.

M168

REV.
A

SCALE

1/1

SOLIDWORKS

SHEET 1 OF 1

DEVICE:

PROJECT: