




REVISIONS					
P.	LTN	DESCRIPTION	DATE	OWN	APPR
M		REVISED PER ECO-13-001003	17JAN2013	DLD	DCS
M1		REVISED PER ECO-14-019263	23DEC2014	DLD	DCS


ASSEMBLY WILL PASS THRU Ø50 OPENING



- △ HOUSING COLORS ARE MECHANICALLY KEYED TO MATE WITH IDENTICALLY COLORED HEADER ASSEMBLIES.
- 2. PLUG MATES TO THE FOLLOWING:
RIGHT ANGLE HEADER - 770669, 776087
VERTICAL HEADER - 776200, 7762228
- 3. PLUG USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854.
- △ DATE CODE ON THIS SURFACE. USES 5 DIGIT CODE:
FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK, LAST DIGIT = DAY.



BOTTOM VIEW WITH LOCKING WEDGE



KEY SLOT LOCATIONS

3, 8 & 16	770680-5
7 & 15	770680-4
4 & 14	770680-3
5 & 11	770680-2
4 & 14	770680-1
KEY SLOT LOCATION (SEE VIEW ABOVE)	PART NUMBER

GLASS FILLED PBT, BLACK	SILICONE RUBBER, GREEN	SILICONE RUBBER, RED	PBT, RED	PBT, BLUE	NONE	770680-5
				PBT, GRAY	NONE	770680-4
				PBT, BLACK	3, 7, 16, 17, 21, 22	770680-3
				PBT, NATURAL	NONE	770680-2
				PBT, BLACK	NONE	770680-1
COVER	WIRE SEAL	MATING SEAL	LOCKING WEDGE	△ HOUSING	CIRCUITS MOLDED CLOSED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN: R. VESTAL 08SEP2009
CHK: D. STRAUSSER 08SEP2009
APPR: D. STRAUSSER 08SEP2009

DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.2
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL: SEE TABLE
FINISH: SEE TABLE

PRODUCT SPEC: 108-1329
APPLICATION SPEC: 114-16016
WEIGHT: -

Customer Drawing

STE TE Connectivity
PLUG ASSEMBLY
23 POSITION AMPSEAL
NOT the LATEST REVISION

A100779C-770680

SCALE: 4:1 SHEET: 1 OF 1