




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
G	ECN 99999: UPDATED DRAWING AND NEW FORMAT	1/20/10	D. FRISIELLO
H	ECN 5937: ADDED NOTE FOR PANEL MOUNTING	1/23/12	D. FRISIELLO



RECOMMENDED PANEL OPENING
(MAX PANEL THICKNESS: 0.06")



FEMALE, 9 PIN
D-SUB CONNECTOR



JACKSCREW
SPECIFICATION

**NOTE: DIFFERENT STANDOFFS AND JACK SCREWS
ARE REQUIRED FOR PANEL MOUNTING.
SEE WWW.L-COM.COM OR MASTER CATALOG FOR DETAILS.**

NOTES:

MATERIAL:
SHELL: STEEL
CONTACTS: COPPER ALLOY
HARDWARE: BRASS
INSULATOR: PBT FIBER REINFORCED (UL94V-0 RATED)

FINISH:
SHELL: TIN/NICKEL PLATED
CONTACTS: GOLD FLASH PLATED, 1-5μ INCHES
HARDWARE: NICKEL PLATED



ELECTRICAL:
CURRENT RATING: 3 AMP
INSULATION RESISTANCE: 1000 MΩ MIN @500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC (FOR ONE MINUTE)

MISCELLANEOUS:
OPERATING TEMPERATURE RANGE: -55°C TO +105°C.
ALL CONTACTS WIRED STRAIGHT THROUGH.
COMPONENT SHALL BE TESTED FOR CONTINUITY.

LABELING:
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC.
"SOCKET SAVER" FONT ARIAL BOLD, TEXT HEIGHTS; .085"
TEXT COLOR; WHITE.

PACKAGING:
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

2X $\begin{matrix} .03^{+.00} \\ -.03 \\ 0 \\ -.762 \end{matrix}$
[0.76]



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM)	APPROVALS	DATE
DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005	DRAWN BY R. CARROLL	09/28/2002
ANGULAR TOLERANCES: ALL = ± 1°	CHECKED BY T. CLARK	09/28/2002
PROJECTION 	APPROVED BY D. PARHAM	09/28/02
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR	

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY D-SUMINIATURE			
PRODUCT DESCRIPTION SOCKET SAVER, DB9 MALE/FEMALE			
SIZE B	PSCM NO. 43321	DWG. NO. DGB9MF	REV. H
SCALE: 2:1	CAD FILE: DGB9MF.SLDDRW	SHEET 1 OF 1	